











P.C.B LAYOUT

DIMENSION

Dim A	N×7.5
Dim B	(N-1)×7.5

N=Number of contacts

Poles	Tolerance
2p-6p	±0.15
7p-12p	±0.25
13p-16p	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
1	3/22'06	Hole size changed from 0.5mm to 1.3mm	Tony
2	01/12'07	Soldering temperature changed from 245° to 250°	Tason
3	01/12'07	Part NO is Changed	Tason
4	07/20'09	The shope of digging hele is Changed	Aaron
5	07/20'09	Operating temperature is Changed	Aaron
6	10/26'09	Wire guard solder pin is Changed from Brass to Copper	Aaron
7	11/09'10	Add is " VDE "	Aaron

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing:Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass Ni plated
- 6 Item 3 Wire guard solder pin:Copper Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-"slot type

7 Electrical	cULus	VDE
Voltage rating: 300VAC		750V
Current rating: 20A		24A
Wire range :		0.2-2.5mm²
Solid wire(AWG): 12-30		
Stranded wire(AWG): 12-30		
Torque(Lb-In): 3.5		0.5 N.m
Screw: M3		
Wire strip length: 6-7mm		
Withstanding Voltage: 1.6KV		3KV

- 5 Operating temperature: -40°C to +115°C
- 2 Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus VDE

3 VJ xx 41 x 0 xxxx G

- xx: No. of poles end stackable sesign
  - 02 2 CONTACTS
  - 03 3 CONTACTS
  - ... ...
  - 16 16 CONTACTS
- x: 0 Black (RAL9005); 2 Red (RAL3001/D); 3 Orange(RAL2011/P); 4 Yellow(RAL1018/A); 5 Green(RAL6018/T); 6 Blue (RAL5015/A); 8 Grey(RAL7035/D)
- xxxx: 0000:"@"Logo (Standard); 000A:"ANYTEK"Logo; Any special item by customer request, please contact sales department.
- G: RoHS Pb<40,000ppm

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VJ-7.5 Series 2P-16P Vertical (90D wire inlet)				
PART NO.	VJxx41x0xxxxG			DWG NO.	8VJ0202
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Aaron 2010.11.09	Aaron 2009.10.26	UNIT: mm / SCALE: NONE / SHEET: 01/01 / REV.: H	

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°