62811-1 ✔ ACTIVE


FASTON | FASTON 250

TE Internal #: 62811-1

Quick Disconnect Receptacle, 18 – 14 AWG, .82 – 2.08 mm² Wire, 6.35 mm [.25 in] Tab Width, Flag, Brass, Unplated Plating, Strip /Reel, FASTON 250

View on TE.com >

Terminals & Splices > Quick Disconnects




Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Termination Features

Product Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Other

Line	Premier
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features

Packaging Quantity	11000
Packaging Method	Strip/Reel

Dimensions

Product Length	16.26 mm[.64 in]
Compatible Insulation Diameter Range	2.79 – 4.06 mm[.11 – .16 in]
Terminal Material Thickness	.51 mm[.02 in]
Wire Size	.82 – 2.08 mm²

Product Type Features

Insertion Force	Normal

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Flag
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



TE Part # 63647-1
250 FASTON FLAG REC 18-14 AWG BR



TE Part # 2150129-2
OCEAN_2.0_Applicator-S-110F180O-RSA




TE Part # 7-2150129-7
OCEAN_2.0_SPARE_PART_KIT-110F180O

Also in the Series | FASTON 250




Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)




Quick Disconnects(425)



Splices(4)

Customers Also Bought




TE Part #1971781-2
PTL RECEPTACLE CONTACT, 14 AWG



TE Part #2-34113-2
SOLIS R 22-16COMM 22-18MIL 1/4



TE Part #2132781-5
05P EP-II HOUSING, NATURAL



TE Part #3-520338-2
ULTRA-FAST 187 ASY REC 16-14 AWG TPBR



TE Part #41531
250 FASTON FLAG REC 18-12 AWG BR




TE Part #520973-1
ULTRA-POD 187 ASSY REC 20-16 AWG BR




TE Part #41333
RING 18-14 AWG TPBR



TE Part #63539-1
250 FASTON REC 14-10 AWG TPBR



TE Part #63482-1
RING 18-14 AWG TPSTL



TE Part #1601028-1
131-064-000=TAB,250X032,STDSMZ

Documents

Product Drawings

250 FASTON FLAG REC 18-14 AWG BR

English

CAD Files

Customer View Model

ENG_CVM_CVM_62811-1_AE.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_62811-1_AE.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_62811-1_AE.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English