





56I-32880111110X

56LED SERIES
 PCB JACK
 (56LED系列PCB接口)
 SHIELD(屏蔽壳):
 3-PULL SHIELD(全包)
 PORTS(插口)
 2-1X2(二口)
 POSITIONS(金针位置):
 8-8POSITIONS(8P)
 CONTACTS(金针根数):
 8-8CONTACTS(8C)

GOLD PLATING(镀金厚度):
 1-FU": 2-1.5U" 3-3U"
 4-6U" 5-15U" 6-30U" 7-50U"
 COLOR(颜色): 1-BLACK(黑色)
 PLASTIC(塑料):
 1-PBT, 2-NYLON66(尼龙66), 3-NYLON46(尼龙46)
 EMI(弹片): 1-W/O EMI(无弹片)
 PIN STYLE(针类型):
 1-ROUND PIN(圆针)
 BACK PEG(后脚铁脚):
 0-W/O BACK PEG(无后背铁脚)
 1-BACK PEG(1个后背铁脚)



PC Board Layout



NOTES:
 ELECTRICAL:
 1. VOLTAGE RATING : 125 VAC RMS.
 2. CURRENT RATING : 1.5 AMP.
 3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
 4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500 VDC.
 5. DIELECTRIC STRENGTH : 1000 VAC RMS 50Hz or 60Hz, 1MIN.
 MECHANICAL:
 1. HOUSING & INSERT MATERIAL : PBT UL94V-0.
 2. CONTACT MATERIAL : DIAMETER 0.45MM PHOSPHOR BRONZE GOLD PLATING OVER NICKEL.
 3. SHIELD : 0.20 ~ 0.25MM THICKNESS BRASS WITH NICKEL PLATED.
 4. MATING/DISMATING FORCE : 2.2KG.F MAX.
 5. RETENTION STRENGTH : 7.7KG.F MIN BETWEEN JACK AND PLUG.
 6. OPERATING LIFE : 600 CYCLES MIN.
 ENVIRONMENTAL:
 1. STORAGE : -10°C ~ +40°C RELATIVE HUMIDITY<70%.
 2. OPERATION : -10°C ~ +85°C.

Remark:
 1. Tolerances Unless Otherwise Specified
 .0±0.25 .00±0.20 .000±0.10
 2. The mark with ★ is the key inspection dimension for QC

REVISION RECORD		
REV	DESCRIPTION	DATE
A/0		2007/08/10
A/1	Update edition	2008/06/05

TELL	1100300006		深圳市连盛精密连接器有限公司	
Fax				
Units	MM	Drawing	yeyouyu	Material
Scale	1 : 1	Check	wangbin	H65V
Rev'	A / 1	Approval	xuxiaorong	PBT
View		Date	2008/06/05	File Name
				Part Number
				SC692