




Solderpot position

A-A





RoHS compliant
by exemption

Cable RG316U double shielded

1731120611	FDX012S102	102
Material Number	FCT Part Number	Material + Finish See extra sheet

Crimping tools:


Crimping of outer conductor:

Hand tool: 1731121732
Die: Y138P cavity B

Pneumatic crimp tool: HX23
(replacement for PH4001)

Extraction tool: DRK38

Cable trimming dimensions



UNLESS OTHERWISE SPECIFIED DIMENSIONS FOR REFERENCE ONLY

REPLACEMENT FOR DOCUMENT NUMBER: FDX012S

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

FUNCTIONAL SYMBOLS
FA = 0
FC = 0
FD = 0

DIVISIONAL SYMBOLS

DIMENSION UNITS: mm
SCALE: 5:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL	± °
4 PLACES	±
3 PLACES	±
2 PLACES	±
1 PLACE	±
0 PLACES	±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 712027
DRWN: VLOKESHA 2021/05/19
CHK'D: MTEUBEL 2022/06/29
APPR: MTEUBEL 2022/06/29

INITIAL REVISION:
DRWN: VLOKESHA 2021/05/19
APPR: MTEUBEL 2022/06/29

molex

FCT 50 OHM COAXIAL CONTACT
FOR EN 60603-2

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
1731120611	PSD	000	A

FIRST ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	A4-SIZE	173112	SEE TABLE	GENERAL MARKET	1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2022/06/29 08:06:06

FORMAT: master-tb-prod-A4
REVISION: J
DATE: 2020/01/14