

Actuator

84-1201.2



<https://eao.com/p/84-1201.2>

Your product:



84-1201.2 Actuator

FRONT

Front dimension: Ø 25 mm

Front bezel colour: Red

Front bezel material: Aluminium

MOUNTING

Mounting cut-out: Ø 22.5 mm

OPERATING-/INDICATION PART

Lens illumination: illuminative

MECHANICAL CHARACTERISTIC

Operating Travel: 1.2 mm

Weight: 0.008 kg

Switching action: Momentary

Switching system: Short-travel element

Mechanical lifetime: ≥1 Mio. cycles of operation

Operating force: 4.0 N ±0.2 N

Tightening torque: Fixing nut 0.8 Nm

AMBIENT CONDITION

IP front protection: IP67

IP Protection: IP67

Operating temperature: - 25 °C ... + 70 °C

Storage temperature: - 40 °C ... + 85 °C

Climate resistance: Damp heat, cyclic: 96 hours, + 25 °C/97 %, + 55 °C/93 % relative humidity, as per EN IEC 60068-2-30
 Damp heat, steady: 56 days, + 40 °C/93 % relative humidity, according to EN IEC 60068-2-78
 Rapid change of temperature: 100 cycles, - 40 °C ... + 80 °C, as per EN / IEC 60068-2-14

CERTIFICATE

Approbations: EBC (TSI PRM), NFF

Conformities: CE, UKCA, 2011 / 65 / EC (RoHS)

OTHER


Short Description: Actuator, Ø 22.5 mm, Ø 25 mm, illuminative, Red, Aluminium, anodised, Momentary, IP67

Dimension: Ø 25 mm


Housing colour: Red

Housing material: Aluminium

Dimension drawings:



Mounting cut-outs:



Wiring diagrams:

