





- 1 SPECIFICATIONS:
MAGNET WIRE #18- #34 AWG.
1.02 [.040]- 0.16 [.006] DIA COPPER,
- 2 POCKET RECOMMENDATION:
#1601425
- 3 SELECTIVE PLATE AREA:
0.00076 [.000030] MIN GOLD PLATE OVER
0.00127 [.000050] MIN NICKEL UNDERPLATE
OVER ENTIRE TERMINAL.
- 4 SELECTIVE PLATE AREA 1.9 MICRONS [.000075] MIN SILVER. ENTIRE
TERMINAL IS UNDERPLATED WITH NICKEL.
- 5 TERMINAL APPLICATION TO COMPLY WITH TYCO
ELECTRONICS SPECIFICATION 114-13166
FIGURE 6.
- 6 NON-STANDARD PACKAGING. ALL PLASTIC REEL AND
PLASTIC INTERLEAVING. PLACED IN A PLASTIC BAG.
- 7 PRELIMINARY - NOT FOR PRODUCTION.



STANDARD	4	—	1601021-5	
6	PRE-TIN PLATE OVER COPPER UNDERPLATE	—	7 3-1601021-4	
STANDARD	3	—	7 2-1601021-3	
STANDARD	3	—	7 1601021-3	
STANDARD	UNPLATED	—	7 1601021-1	
STANDARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	—	3-1601021-2	
STANDARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	131-046-014	2-1601021-2	
STANDARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	131-047-014	1601021-2	
PACKAGING	FINISH	REFERENCE PART NUMBER	TE PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.WELLER 11JAN2002	TE TE Connectivity	
		CHK M.FEHER 11JAN2002		
DIMENSIONS: mm [INCHES]		APVD K.RANDOLPH 11JAN2002	NAME STD RANGE WIRE TO .187 X .020 MULTI-BARB TAB SIAMEZE TERMINAL	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 		PRODUCT SPEC 108-2085		
		APPLICATION SPEC 5	SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-1601021 —	
MATERIAL BRASS, FULL HARD	FINISH SEE TABLE	WEIGHT —		
CUSTOMER DRAWING		SCALE 9:1	SHEET 1 OF 1	REV G6