

SIGN	DATE	DESCRIPTION	APPROVER
△	01.11'06	Standard spec is changed.	xionghaitao
△	10/9'06	VDE wire range changed from 0.75-1.5mm ² to 0.75-4.0mm ²	Steady
△	10/9'06	Solid wire and Stranded wire changed from 12-18 to 12-20	Steady

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!

Material

- Terminal body
- (metal housing): Brass Stamped
- Terminal screw: Steel Zinc plating "+/-" slot type
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)





△ **Electrical** cULus/VDE

- Voltage rating: 300VAC/450VAC
- Current rating: 10A/17.5A
- Wire range: 0.75-4.0mm²
- Solid wire(AWG): 12-20
- Stranded wire(AWG): 12-20
- Torque: 3.5Lb-In/0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- SAFETY APPROVAL DETA:



T4 xx 04 x x xxxx G

02	2 CONTACTS	0	Black	0	4.4mm	0000 @ logo	RoHS
03	3 CONTACTS	5	Green	1	3.0mm	0091 ANY logo	Pb<40,000ppm
...	...	6	Blue			Any special item by customer request,	
24	24 CONTACTS	8	Grey			please contact sales department.	



N = Number of poles
 Dim L = N x 5.0
 Dim P = (N-1) x 5.0

	Dim L	Dim P
2-6p	±0.20	±0.15
7-12p	±0.25	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

RECOMMENDED P.C.B. LAYOUT

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		T4-5.0mm 2P-30P		DWG NO.		8T40001	
PART NO.		T4xx04xxxxxxG		DWG NO.		8T40001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		Steady	Steady			X. ±0.50	
		2006.10.09	2006.10.09			X.X ±0.30	
				SHEET: 01/01		X.XX ±0.10	
						X° ±1°	