




NOTES:

- ADAPTER MEETS:
CAT5e: TIA/EIA-568-B.2 STANDARD
CAT6: TIA/EIA-568-B.2-1 STANDARD
CAT6A: TIA/ANSI-568-C.2 STANDARD
- MATERIALS:
RJ45 MOUNTING PLATE - ZINC ALLOY, BLACK OR NICKEL PLATED
RJ45 HOUSING - THERMOPLASTIC, BLACK
RJ45 SHIELD - COPPER ALLOY, NICKEL PLATED
- FOR SCREWS TO BE SHIPPED WITH ASSEMBLY, ADD SUFFIX PKG TO PART NUMBER.
- WHEN MOUNTING ASSEMBLY, USE A SCREW TORQUE OF 10 INCH-LBS MAXIMUM.
- THIS PRODUCT IS RoHS COMPLIANT.

RECOMMENDED PANEL CUT-OUT

PART NUMBER	RJ45 ADAPTER
NHRJ45D5EB	CAT5e UNSHIELDED
NHRJ45D5ES	CAT5e SHIELDED
NHRJ45D6B	CAT6 UNSHIELDED
NHRJ45D6S	CAT6 SHIELDED
NHRJ45D6AB	CAT6A UNSHIELDED
NHRJ45D6AS	CAT6A SHIELDED

CUSTOMER DRAWING

SIZE	WIDTH	MULT	LBS/M	TEMPER
FINISH				
SPEC No.				
FIRST USED ON				
SCALE 1.5:1				
DATE DRAWN	BY	CHKD	APVD	
7/30/21	NS	7/30/21	7/30/21	
NAME				
NH SERIES				
RJ45 ADAPTER, RoHS				
PART No.				
NHRJ45D SERIES				
REV				
A				

DO NOT SCALE DRAWING

SolidWorks CAD File