OLGA-S

~11° spot beam beam. Assembly with holder and installation tape.



SPECIFICATION:

Dimensions	Ø 32.0 mm
Height	19.1 mm
Fastening	tape, pin
ROHS compliant	yes


MATERIALS:

Component	Type	Material	Colour	Finish
OLGA-S	Single lens	PMMA	clear	
OLGA-HLD	Holder	PC	black	
SPUTNIK-TAPE3	Tape	Acrylic foam	black	

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CA16127_OLGA-S » Box size: 476 x 273 x 292 mm	Single lens	792	132	66	9.8

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.



See also our general installation guide: www.ledil.com/installation_guide


LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

CREE LEDs

LED	XD16
FWHM / FWTM	13.0° / 28.0°
Efficiency	82 %
Peak intensity	10.4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






CREE LEDs

LED	XHP35 HD
FWHM / FWTM	19.0° / 37.0°
Efficiency	83 %
Peak intensity	5.5 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






CREE LEDs

LED	XHP35 HI
FWHM / FWTM	15.0° / 31.0°
Efficiency	87 %
Peak intensity	8.5 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






CREE LEDs

LED	XHP50
FWHM / FWTM	24.0° / 44.0°
Efficiency	83 %
Peak intensity	3.7 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

CREE LEDs

LED	XHP50.2
FWHM / FWTM	23.0° / 43.0°
Efficiency	82 %
Peak intensity	4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







CREE LEDs

LED	XM-L
FWHM / FWTM	17.0° / 34.0°
Efficiency	86 %
Peak intensity	6.8 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







CREE LEDs

LED	XM-L3
FWHM / FWTM	17.0° / 35.0°
Efficiency	85 %
Peak intensity	6.5 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







CREE LEDs

LED	XP-E
FWHM / FWTM	11.0° / 27.0°
Efficiency	87 %
Peak intensity	12.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

CREE LEDs


LED	XP-E2
FWHM / FWTM	11.0° / 26.0°
Efficiency	89 %
Peak intensity	13.6 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






CREE LEDs

LED	XP-G2
FWHM / FWTM	13.0° / 29.0°
Efficiency	87 %
Peak intensity	10 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






CREE LEDs


LED	XP-G3
FWHM / FWTM	14.0° / 31.0°
Efficiency	86 %
Peak intensity	8.4 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






CREE LEDs

LED	XP-L HI
FWHM / FWTM	14.0° / 29.0°
Efficiency	88 %
Peak intensity	10.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

CREE LEDs

LED	XP-L2
FWHM / FWTM	18.0° / 36.0°
Efficiency	82 %
Peak intensity	5.8 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






CREE LEDs

LED	XQ-E HD
FWHM / FWTM	11.0° / 28.0°
Efficiency	81 %
Peak intensity	11 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







CREE LEDs

LED	XQ-E HI
FWHM / FWTM	11.0° / 26.0°
Efficiency	86 %
Peak intensity	13.6 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







CREE LEDs

LED	XT-E
FWHM / FWTM	14.0° / 30.0°
Efficiency	84 %
Peak intensity	8.8 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

LUMILEDS

LED	LUXEON C
FWHM / FWTM	11.0° / 27.0°
Efficiency	84 %
Peak intensity	11.6 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







LUMILEDS

LED	LUXEON CZ
FWHM / FWTM	11.0° / 25.0°
Efficiency	89 %
Peak intensity	14.8 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






LUMILEDS

LED	LUXEON M/MX
FWHM / FWTM	24.0° / 44.0°
Efficiency	84 %
Peak intensity	3.8 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







LUMILEDS

LED	LUXEON MZ
FWHM / FWTM	19.0° / 35.0°
Efficiency	86 %
Peak intensity	6.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

LUMILEDS


LED	LUXEON Rebel ES
FWHM / FWTM	14.0° / 30.0°
Efficiency	86 %
Peak intensity	9.5 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






LUMILEDS

LED	LUXEON TX
FWHM / FWTM	14.0° / 29.0°
Efficiency	86 %
Peak intensity	9.8 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






LUMILEDS

LED	LUXEON V
FWHM / FWTM	18.0° / 35.0°
Efficiency	84 %
Peak intensity	6.5 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






LUMILEDS

LED	LUXEON V2
FWHM / FWTM	15.0° / 31.0°
Efficiency	86 %
Peak intensity	9 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	







LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

LUMILEDS


LED	LUXEON Z
FWHM / FWTM	11.0° / 25.0°
Efficiency	88 %
Peak intensity	15.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






LUMILEDS


LED	LUXEON Z ES
FWHM / FWTM	12.0° / 27.0°
Efficiency	89 %
Peak intensity	12.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






NICHIA

LED	NCSxE17A
FWHM / FWTM	12.0° / 26.0°
Efficiency	87 %
Peak intensity	12.7 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






NICHIA

LED	NV4x144A
FWHM / FWTM	23.0° / 43.0°
Efficiency	84 %
Peak intensity	4.1 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

NICHIA


LED	NVSW219D
FWHM / FWTM	14.0° / 30.0°
Efficiency	85 %
Peak intensity	9.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






NICHIA


LED	NVSW319B
FWHM / FWTM	16.0° / 33.0°
Efficiency	86 %
Peak intensity	7.4 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






NICHIA

LED	NVSxE21A
FWHM / FWTM	14.0° / 28.0°
Efficiency	87 %
Peak intensity	10.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






NICHIA

LED	NVSxx19B/NVSxx19C
FWHM / FWTM	15.0° / 31.0°
Efficiency	85 %
Peak intensity	8.8 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors

LED	Duris S8
FWHM / FWTM	24.0° / 43.0°
Efficiency	86 %
Peak intensity	4.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







OSRAM
Opto Semiconductors

LED	OSCONIQ P 3737 (2W version)
FWHM / FWTM	14.0° / 30.0°
Efficiency	87 %
Peak intensity	9.2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






OSRAM
Opto Semiconductors

LED	OSCONIQ P 3737 (3W version)
FWHM / FWTM	17.0° / 33.0°
Efficiency	86 %
Peak intensity	7.2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






OSRAM
Opto Semiconductors

LED	OSCONIQ P 7070
FWHM / FWTM	23.0° / 42.0°
Efficiency	84 %
Peak intensity	4.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors

LED	OSLON Black Flat (LUW HWQP)
FWHM / FWTM	11.0° / 24.0°
Efficiency	88 %
Peak intensity	16 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







OSRAM
Opto Semiconductors

LED	OSLON Square CSSRM2/CSSRM3
FWHM / FWTM	14.0° / 30.0°
Efficiency	87 %
Peak intensity	10.2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






OSRAM
Opto Semiconductors

LED	OSLON Square EC
FWHM / FWTM	13.0° / 29.0°
Efficiency	85 %
Peak intensity	10 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







OSRAM
Opto Semiconductors

LED	OSLON Square PC
FWHM / FWTM	13.0° / 30.0°
Efficiency	85 %
Peak intensity	10.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

OSRAM Opto Semiconductors

LED	OSLON SSL 150
FWHM / FWTM	11.0° / 26.0°
Efficiency	87 %
Peak intensity	13 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







OSRAM Opto Semiconductors

LED	OSLON SSL 80
FWHM / FWTM	13.0° / 28.0°
Efficiency	86 %
Peak intensity	11.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







OSRAM Opto Semiconductors

LED	OSTAR Stage (S2WN)
FWHM / FWTM	14.0° / 30.0°
Efficiency	86 %
Peak intensity	9.3 cd/lm
LEDs/each optic	1
Light colour	RGBW

Required components:






SAMSUNG

LED	LH181A
FWHM / FWTM	15.0° / 30.0°
Efficiency	81 %
Peak intensity	8.4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

SAMSUNG


LED	LH181B
FWHM / FWTM	15.0° / 29.0°
Efficiency	87 %
Peak intensity	9.7 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






SAMSUNG


LED	LH231B
FWHM / FWTM	16.0° / 31.0°
Efficiency	88 %
Peak intensity	8.6 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






SAMSUNG


LED	LH351B
FWHM / FWTM	14.0° / 30.0°
Efficiency	87 %
Peak intensity	9.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






SAMSUNG

LED	LH351C
FWHM / FWTM	15.0° / 31.0°
Efficiency	86 %
Peak intensity	8.5 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

SAMSUNG

LED	LH351D
FWHM / FWTM	18.0° / 36.0°
Efficiency	85 %
Peak intensity	6.2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







SAMSUNG

LED	LH508A
FWHM / FWTM	21.0° / 40.0°
Efficiency	86 %
Peak intensity	4.9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






SAMSUNG

LED	LM302A
FWHM / FWTM	14.0° / 30.0°
Efficiency	89 %
Peak intensity	9.9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







SAMSUNG

LED	LM561B
FWHM / FWTM	14.0° / 31.0°
Efficiency	88 %
Peak intensity	9.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

SEOUL SEMICONDUCTOR

LED	WICOP 5050
FWHM / FWTM	24.0° / 45.0°
Efficiency	81 %
Peak intensity	3.6 cd/lm
LEDs/each optic	1
Light colour	White

Required components:







SEOUL SEMICONDUCTOR

LED	Z5M3
FWHM / FWTM	16.0° / 32.0°
Efficiency	84 %
Peak intensity	7.7 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (SIMULATED):


CREE LEDs

LED	XHP50.3 HD
FWHM / FWTM	22.0° / 40.0°
Efficiency	84 %
Peak intensity	4.8 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




CREE LEDs

LED	XHP50.3 HI
FWHM / FWTM	18.0° / 36.0°
Efficiency	95 %
Peak intensity	6.4 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




CREE LEDs

LED	XHP70.3 HD
FWHM / FWTM	26.0 + 28.0° / 50.0°
Efficiency	82 %
Peak intensity	3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



CREE LEDs

LED	XP-E2
FWHM / FWTM	11.0° / 28.0°
Efficiency	91 %
Peak intensity	12.7 cd/lm
LEDs/each optic	1
Light colour	Amber
Required components:	




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (SIMULATED):


CREE LEDs

LED	XP-G2 HE
FWHM / FWTM	15.0° / 32.0°
Efficiency	88 %
Peak intensity	8.7 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




LUMILEDS

LED	LUXEON 7070
FWHM / FWTM	26.0° / 51.0°
Efficiency	94 %
Peak intensity	3.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




LUMINUS

LED	SST-20
FWHM / FWTM	14.0° / 28.0°
Efficiency	91 %
Peak intensity	11.7 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LUMINUS

LED	SST-70X-WCS
FWHM / FWTM	20.0° / 37.0 + 36.0°
Efficiency	89 %
Peak intensity	6.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (SIMULATED):


NICHIA

LED	NFMW48xA
FWHM / FWTM	21.0° / 40.0°
Efficiency	89 %
Peak intensity	5.5 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




NICHIA

LED	NV4WB35AM
FWHM / FWTM	18.0° / 34.0°
Efficiency	89 %
Peak intensity	7.2 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



SAMSUNG

LED	LH151B
FWHM / FWTM	22.0° / 38.0°
Efficiency	88 %
Peak intensity	5.1 cd/lm
LEDs/each optic	4
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support
www.ledil.com/
where_to_buy

Shipping locations
Salo, Finland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.