

SIGN	DATE	DESCRIPTION	APPROVER
△	02.05'13	Update the drawing	Chen Bo
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item① Terminal body: Brass(CuZn),Tin plated
- Item② Terminal screw: Steel Zinc plating "--" slot type
- Item③ Wire guard: Stainless steel
- Item④ Terminal housing:Thermoplastic (UL94 V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-22
- Stranded wire(AWG): 14-22
- Torque: 3.5Lb-In
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- SAFETY APPROVAL DATA: 
- Critical dimension: ▽

VA xx 2 1 x 0 xxxx G

End Stackable
02 02 CONTACTS
03 03 CONTACTS
...
16 16 CONTACTS





Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- C Green(RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy

0000 "@" Logo
000A "ANY" Logo

Any special item by
customer request,
please contact sales
department



P.C.B Layout
Top view

N = Number of poles

Dim L=Nx7.5

Dim P=(N-1)x7.5

	Dim P	Dim L
2-4p	±0.10	±0.15
5-8p	±0.20	±0.20
9-12p	±0.25	±0.30
13-16p	±0.30	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VA -7.5mm Series						
PART NO.		VAxx21x0xxxxG			DWG NO.	8VA0101		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Chen Bo 02/05'13	Chen Bo 02/05'13		UNIT: mm		X.	±0.50
					SCALE: NONE		X.X	±0.30
				SHEET: 01/01	REV.: D		X.XX	±0.10
							X°	±1°