

APPLICABLE FPC/FFC
RECOMMENDED DIMENSION
(THICKNESS:0.30±0.03)


50	29.10	24.50	27.50	25.60
49	28.60	24.00	27.00	25.10
48	28.10	23.50	26.50	24.60
47	27.60	23.00	26.00	24.10
46	27.10	22.50	25.50	23.60
45	26.60	22.00	25.00	23.10
44	26.10	21.50	24.50	22.60
43	25.60	21.00	24.00	22.10
42	25.10	20.50	23.50	21.60
41	24.60	20.00	23.00	21.10
40	24.10	19.50	22.50	20.60
39	23.60	19.00	22.00	20.10
38	23.10	18.50	21.50	19.60
37	22.60	18.00	21.00	19.10
36	22.10	17.50	20.50	18.60
35	21.60	17.00	20.00	18.10
34	21.10	16.50	19.50	17.60
33	20.60	16.00	19.00	17.10
32	20.10	15.50	18.50	16.60
31	19.60	15.00	18.00	16.10
30	19.10	14.50	17.50	15.60
29	18.60	14.00	17.00	15.10
28	18.10	13.50	16.50	14.60
27	17.60	13.00	16.00	14.10
26	17.10	12.50	15.50	13.60
25	16.60	12.00	15.00	13.10
24	16.10	11.50	14.50	12.60
23	15.60	11.00	14.00	12.10
22	15.10	10.50	13.50	11.60
21	14.60	10.00	13.00	11.10
20	14.10	9.50	12.50	10.60
19	13.60	9.00	12.00	10.10
18	13.10	8.50	11.50	9.60
17	12.60	8.00	11.00	9.10
16	12.10	7.50	10.50	8.60
15	11.60	7.00	10.00	8.10
14	11.10	6.50	9.50	7.60
13	10.60	6.00	9.00	7.10
12	10.10	5.50	8.50	6.60
11	9.60	5.00	8.00	6.10
10	9.10	4.50	7.50	5.60
9	8.60	4.00	7.00	5.10
8	8.10	3.50	6.50	4.60
7	7.60	3.00	6.00	4.10
6	7.10	2.50	5.50	3.60
5	6.60	2.00	5.00	3.10
4	6.10	1.50	4.50	2.60
No. of Contacts	A	B	C	D

1.MATERIAL:

- 1.1 HOUSING: High Temperature Plastic,UL94V-0;
COLOR: NATURE.
- 1.2 ACTUATOR: High Temperature Plastic,UL94V-0;
COLOR: BLACK.
- 1.3 CONTACT: Copper alloy,T=0.15±0.01mm
- 1.4 SOLDER PAD: Copper alloy,T=0.20±0.01mm

2.FINISH:

- 2.1 CONTACT:TIN PLATED IN SOLDER AREA
NICKEL UNDERPLATED OVERALL.
- 2.2 SOLDER PAD:TIN PLATED IN SOLDER AREA
NICKEL UNDERPLATED OVERALL.

 深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 0.5PH 1.5H 翻盖下接FPC
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW5C-05FPCXX-150B
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2604271101
			SHEET NO. 1 OF 1