


Specification Sheet

Part Number: 156-02434

Versatile and robust fir tree design provides low insertion effort yet delivers exceptional retention strength in an 6.5 mm hole and M8 threaded hole. Wider and thinner strap design increases flexibility and minimizes pinching of bundles, hoses and tubing.

PA46 nylon material provides great performance at up to 135°F continuous operating temperature.



2-Piece Cable Tie/Fir Tree Mount, 6.5mm Hole and M8 Threaded Hole, PA46, Brown, 1200/ctn

Article Number 156-02434

Type WSSDFTM8WSSDSET

Color Brown (BN)

Quantity Per bag

Product Description These two-piece fasteners are pre-assembled and offer a simple and versatile method of bundling and mounting cables. Sold as an unassembled set, this oval fir tree and tie combination allows the user to install the tie in two different directions, securing the bundle perpendicular or inline to the oval mounting hole.

Short Description 2-Piece Cable Tie/Fir Tree Mount, 6.5mm Hole and M8 Threaded Hole, PA46, Brown, 1200/ctn

Global Part Name WSSDFTM8WSSDSET-PA46-BN

Minimum Tensile Strength (Imperial) 120.0

Minimum Tensile Strength (Metric) 533.0

Length L (Imperial) 9.1

Length L (Metric) 231.14

Fixation Method Fir Tree

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.88

Width W (Metric) 22.6

Bundle Diameter Min (Imperial) 0.37

Bundle Diameter Min (Metric) 9.4

Bundle Diameter Max (Imperial) 2.25

Bundle Diameter Max (Metric) 57.15

Height H (Imperial)	0.89
Height H (Metric)	22.77
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.23
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.28
Mounting Hole Diameter D (Metric)	6.1 - 7.0 mm M8 Threaded
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.0
Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
Flammability	UL 94 V-2
Halogen Free	Yes

UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1200
Package Quantity (Metric)	1200
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)