




Poles	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16
Dim L	19.04	28.56	38.08	47.60	57.12	66.64	76.16	85.68	95.20	104.72	114.24	123.76	133.28	142.80	152.32
Dim B	9.52	19.04	28.56	38.08	47.60	57.12	66.64	76.16	85.68	95.20	104.72	114.24	123.76	133.28	142.80
TOL	±0.20					±0.30					±0.40				

SIGN	DATE	DESCRIPTION	APPROVER
△	9/06'07	Screw is changed from M3.0 to M3.5	Marvin
△	9/06'07	The Electrical is changed	Marvin
△	7/4'09	Current ,operating temperature are changed	Jody
△	10/08'09	Change the Body surface and its back into matt surface	Aaron
△	10/21'09	Wire guard solder pin is changed from Brass to Copper	Aaron
△	02/22'10	Torque is changed from 8.9Lb-In to 6.9Lb-In	Aaron
△	08/03'10	Clamp is changed	Aaron
△	12/13'10	Add is " TUV "	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing : Thermoplastic (UL 94V-0)
 - Item 2 Clamp: Brass ,Ni plated
 - △ Item 3 Wire guard solder pin: Copper, Tin plated
 - Item 4 Terminal screw: Steel Zinc plating"- "slot type
- △ Electrical cULus TUV
- Voltage rating: 300VAC 750VAC
 - Current rating: 30A 41A
 - Wire range: 0.20-6.0mm²
 - △ ● Solid wire(AWG): 10-24
 - △ ● Stranded wire(AWG): 10-24
 - △ ● Torque(Lb-In): 6.9 0.85 N.m
 - △ ● Screw: M3.5
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 1.6KV 3.0KV
 - △ ● Operating temperature: -40°C to +115°C
 - Soldering temperature: 250°C±10°C/5 Sec
 - Safety Approval:

T7 xx 23 x 0 xxxx G

No. of poles end stackable design	0	Black (RAL9005)	RoHS
02 2 CONTACTS	2	Red (RAL3001/D)	Pb<40,000ppm
03 3 CONTACTS	3	Orange(RAL2011/P)	0000 Standard @ Logo
...	4	Yellow(RAL1018/A)	000A Standard ANY Logo
...	5	Green(RAL6018/T)	Any special item by customer request,
16 16 CONTACTS	6	Blue (RAL5015/A)	please contact sales department.
	8	Grey(RAL7035/D)	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		T7 9.52 SERIES 180D							
PART NO.		T7xx23x0xxxxG			DWG NO.	8T70101			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
			Chen Bo 2010.12.13					UNIT: mm	
					SCALE: NONE		X.X	±0.30	
					REV. K		X.XX	±0.10	
					SHEET: 01/01		X°	±1°	