





1

2

3

4



Technical requirements:

- 1、Unit: mm
- 2、Wire diameter: 0.3
- 3、Material: Nickel Plated Steel-Wire, meet ROHS
- 4、Style: horn mouth center
- 5、Technics: High-Temperature Heat Treatment at 260°C
- 6、Size tolerance: The tolerance of unmarked parts is $\pm 0.25\text{mm}$
- 7、No dirty surface, no bad material
- 8、Contact number: 13459252012、0592-5216722
- 9、Mode: F4-6-2-0.3Z
- 10、Salt spray test: five percent salt spray test meets 24 hours
- 11、Package: by bag, MPQ: 2000PCS/bag

碳钢线

厦门市芯网电子
科技有限公司

标记	处数	分区	更改文件号	签名	年月日	阶段标记	重量	比例
设计						s		5:1
校核								
批准								

1

2

3

4