



深圳市兴华鑫电子科技有限公司

Shenzhen xinghuaxin Electronic Technology Co., Ltd

承認書

SPECIFICATION FOR APPROVAL

客戶 (Customer): _____

客戶料號 (Customer P/N): _____

興華鑫型號 (Supplier P/N): _____

2316-DC12V

產品名稱 (Description): _____

蜂鸣器 (Buzzer)

產品規格 (Specification): _____

23*16MM 有源压电式

客戶承認欄 (Customer Authorization Signature)	深圳市興華鑫電子科技有限公司 承認欄 (Supplier Audit)		
	審核	檢查	制作
	唐国兴	唐玉来	吴银娟
	日期: 2022 年 04 月 19 日		
	版次: A		

声音让生活更精彩!

地址: 深圳市宝安区新安街道新乐社区新乐路 88 号厂房四层

TEL: 0755-27892904

E-mail: jacky.tang@jsxhxdz.com

Http: www.jsxhxdz.com

深圳市兴华鑫电子科技有限公司

产品规格内容

Customer:		Part No:		
Product: Piezoelectric Buzzers		XHXDZ Part No: XHXDZ-2316-DC12V		
Technical Terms				
Resonant Frequency (KHZ)		3.2±0.5		
Rated Voltage (V_{DC})		12		
Operating Voltage (V_{DC})		3~20		
Max. Current Consumption at Rated Voltage (mA)		25		
Min. Sound Output at 10cm at Rated Voltage (dB)		90		
Operating Temperature (°C)		-20~+70		
Storage Temperature (°C)		-30~+80		
Environmental Protection Regulation				
Buzzer		Soldering Parameter		
Soldering process		Temp.(°C)	Time(Sec.)	Times
Inclusive Lead	Reflow soldering	230±10	above 170°C time 40~70	2
	Wave soldering	245±5	3~6	1~2
	Manual soldering	330±10	1~2	1~2
Lead Free	Reflow soldering	245±15	above 180°C time 40~70	3
	★ Wave soldering	260±5	4~8	2~3
	★ Manual soldering	350±10	1~3	2~3

Remark: ★XHXDZ Instance Soldering Process

APPEARANCE DRAWING Tol : ± 0.5 Unit: mm

