


SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

Reverse Voltage - 20 to 200 Volts Forward Current - 3.0 Ampere

Features

- Metal silicon junction, majority carrier conduction
- For surface mounted applications
- Low power loss, high efficiency
- High forward surge current capability
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

DO-214AA/SMB **RoHS**
COMPLIANT



Cathode Band

Mechanical Data

Case : DO-214AA/SMB molded plastic body

Terminals :Solderable per MIL-STD-750,Method2026

Polarity : Cathode line denotes the cathode end

Position: Any

Approx. Weight : 0.095g / 0.003oz

Equivalent circuit



Absolute Maximum Ratings and Electrical characteristics

Ratings at 25°C ambient temperature unless otherwise specified.Single phase, half wave, 60Hz resistive or inductive load,for capacitive load,derate by 20 %

Parameter	SYMBOLS	SS32B	SS34B	SS36B	SS38B	SS310B	SS312B	SS315B	SS320B	UNITS
		SS32	SS34	SS36	SS38	SS310	SS312	SS315	SS320	
Maximum repetitive peak reverse voltage	V_{RRM}	20	40	60	80	100	120	150	200	V
Maximum RMS voltage	V_{RMS}	14	28	42	56	70	84	105	140	V
Maximum DC blocking voltage	V_{DC}	20	40	60	80	100	120	150	200	V
Maximum average forward rectified current at $T_c=100\text{C}$	$I_{F(AV)}$	3.0								A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	80								A
Maximum instantaneous forward voltage at 3.0A	V_F	0.55		0.70		0.85		0.95		V
Maximum DC reverse current at rated DC blocking voltage $T_A=25\text{C}$ $T_A=125\text{C}$	I_R	0.5			0.3					mA
		5.0			3.0					
Typical junction capacitance (NOTE 1)	C_J	450			400					pF
Typical thermal resistance (NOTE 2)	$R_{\theta JA}$	60								°C/W
Operating junction temperature range	T_J	-55 to +150								°C
Storage temperature range	T_{STG}	-55 to +150								°C

Note:1.Measured at 1MHz and applied reverse voltage of 4.0V D.C.

2.PC.B.mounted with 0.2"X0.2"(5 X5 mm) copper pad areas.

Typical Characteristics

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic




Fig.4 Typical Junction Capacitance




Fig.5 Maximum Non-Repetitive Peak Forward Surge Current






Fig.6 Typical Transient Thermal Impedance




DO-214AA/SMB Package Outline Dimensions



Symbol	imensions In Millimeters		imensions In Inches	
	Min	Max	Min	Max
A	2.13	2.44	0.084	0.096
C	0.15	0.31	0.006	0.012
D	3.30	3.95	0.130	0.156
E	4.06	4.70	0.160	0.185
E ₁	5.08	5.59	0.200	0.220
b	1.90	2.20	0.075	0.087
L	0.80	1.50	0.031	0.059
A ₁	0.2 REF		0.008 REF	

DO-214AA/SMB Suggested Pad Layout



- Note:
1. Controlling dimension: in/millimeters.
 2. General tolerance: $\pm 0.05\text{mm}$.
 3. The pad layout is for reference purposes only.