GUANGDONG TONGJIA OPTOELECTRONICS TECHNOLOGY CO., LTD

承认书

Specification For Approval

Customer: (客戶) _____

Description:产品描述) SMD3014灯珠侧发0.1W黄光

Part number:(产品型号) TJ-S3014SLUG1W5TLC9Y-A5

Date: (日期) _____

Approved By: (客户承认)

Prepared By:(我司承认)

Approval	Check	Design	Sales
核准	審核	製作	業務

Customer Service Hotline：**400-676-8616**

TEL：0769-8662 5999　　0769-8200 2226　　FAX：0769-8200 2227

E-MIAL：dg@togialed.com　　WEB：www.togialed.com

Features

3.0mm x 1.38mm SMT LED, 1.5mm thickness


Low power consumption

Wide view angle


Package: 4000pcs/reel

RoHS Compliant

Package outlines



Recommend Pad Layout





ATTENTION

OBSERVE PRECAUTIONS FOR HANDLING ELECTROSTATIC SENSITIVE DEVICES

Notes:

1. All dimensions are in millimeters (inches);
2. Tolerances are ±0.1mm (0.004inch) unless otherwise noted.


Absolute maximum ratings (TA=25℃)


Parameter	Symbol	Value	Unit
Forward current	If	30	mA
Reverse voltage	Vr	5	V
Power dissipation	Pd	78	mW
Operating temperature	Top	-20 ~+80	℃
Storage temperature	Tstg	-30 ~+85	℃
Peak pulsing current (1/8 duty f=1kHz)	Ifp	125	mA


Electro-optical characteristics (TA=25℃)


Parameter	Test Condition	Symbol	Value			Unit
			Min	Typ	Max	
Wavelength at peak emission	If=30mA	λp	--	590	--	nm
Spectral half bandwidth	If=30mA	△λ	--	18	--	nm
Dominant wavelength	If=30mA	λd	585	--	595	nm
Forward voltage	If=30mA	Vf	1.8	--	2.4	V
Luminous intensity	If=30mA	Iv	800	--	1200	mcd
Viewing angle at 50% Iv	If=10mA	2θ1/2	--	120	--	Deg
Reverse current	Vr=5V	Ir	--	--	10	μA


Optical characteristic curves















Reflow Profile

■ Reflow Temp/Time



Notes:

1.We recommend the reflow temperature 245℃(±5℃).the maximum soldering temperature should be limited to 260℃.

2.Don't cause stress to the epoxy resin while it is exposed to high temperature.

3.Number of reflow process shall be 2 times or less.

■Soldering iron


Basic spec is ≤ 5sec when 260℃. If temperature is higher, time should be shorter (+10℃→ -1sec).Power dissipation of iron should be smaller than 20W, and temperatures should be controllable .Surface temperature of the device should be under 230℃ .

■Rework

1.Customer must finish rework within 5 sec under 260℃.

2.The head of iron can not touch copper foil


3.Twin-head type is preferred.



■ Avoid rubbing or scraping the resin by any object, during high temperature, for example reflow solder etc.

Test circuit and handling precautions

■ Test circuit



■ Handling precautions

1. Over-current-proof

Customer must apply resistors for protection; otherwise slight voltage shift will cause big current change (Burn out will happen).

2. Storage

2.1 It is recommended to store the products in the following conditions:

Humidity: 60% R.H. Max.

Temperature : 5℃~30℃(41℉~86℉)

2.2 Shelf life in sealed bag: 12 month at ＜5℃~30℃ and ＜30% R.H. after the package is Opened, the products should be used within a week or they should be keeping to stored at≦20 R.H. with zip-lock sealed.

3. Baking

It is recommended to baking before soldering when the pack is unsealed after 72hrs. The Conditions are as followings:

3.1 60±3℃ x(12~24hrs) and ＜5%RH, taped reel type

3.2 100±3℃ x(45min~1hr), bulk type


3.3 130±3℃ x(15~30min), bulk type

Test items and results of reliability


Type	Test Item	Test Conditions	Note	Number of Damaged
Environmental Sequence	Temperature Cycle	-20℃ 30min ↑ ↓ 80℃ 30min	100 cycle	0/22
	Thermal Shock	-20℃ 15min ↑ ↓ 80℃ 15min	100 cycle	0/22
	High Humidity Heat Cycle	30℃⇔ 65℃ 90%RH 24hrs/1cycle	10 cycle	0/22
	High Temperature Storage	Ta=80℃	1000 hrs	0/22
	Humidity Heat Storage	Ta=60℃ RH=90%	1000 hrs	0/22
	Low Temperature Storage	Ta=-30℃	1000 hrs	0/22
Operation Sequence	Life Test	Ta=25℃ IF=30mA	1000 hrs	0/22
	High Humidity Heat Life Test	60℃ RH=90% IF=30mA	500 hrs	0/22
	Low Temperature Life Test	Ta=-20℃ IF=30mA	1000 hrs	0/22

3014 Series SMD LED Lamps Packaging Specifications


- Feeding Direction




- Dimensions of Reel (Unit: mm)



- Dimensions of Tape (Unit: mm)



- Arrangement of Tape




Notes:

1. Empty component pockets are sealed with top cover tape;
2. The maximum number of missing lamps is two;
3. The cathode is oriented towards the tape sprocket hole in accordance with ANSI/EIA RS-481 specifications.
4. 4,000 pcs/Reel.

3014 Series SMD LED Lamps Packaging Specifications

- Packaging specifications



Notes:

Reeled products (numbers of products are 4,000pcs) packed in a seal off moisture-proof bag along with a desiccant one by one, Seven moisture-proof bag of maximums (total maximum number of products are 40,000pcs) packed in an inside box (about size: 260x 220x 130mm) and four inside boxes of maximums are put in the outside box (about size: 450mm x 260mm x 400mm) Together with buffer material, and it is packed. (Part No., Lot No., quantity should appear on the label on the moisture-proof bag, part No. And quantity should appear on the label on the cardboard box.) The number of the loading steps of outside box (cardboard box) has it to three steps.