



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **5.08 mm [.2 in]**

Number of Rows: **1**

Features

Product Type Features

Header Type	Fully Shrouded
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Green
Product Orientation	Right Angle



Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	15 A

Termination Features

Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Dimensions

Wire Size	.05 – 3 mm²
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	150
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free












Solder Process Capability

Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 796634-4 4 POS 5.08MM R/A PLUG,TRM BLK	 TE Part # 284041-4 TERMINAL BLOCK VERTICAL PLUG S	 TE Part # 282807-4 TERMI-BLOK PLUG STACKING 4P.5,	 TE Part # 1986262-4 4 POS PLUG SPRING CONN, PITCH 5.08
 TE Part # 284047-4 TERMI-BLOK VERTICAL PLUG STACK	 TE Part # 1776038-4 4P 5.08 R/A HDR,CLOSED END	 TE Part # 796635-4 4 POS 5.08MM R/A PLUG,TRM BLK	 TE Part # 2-284041-9 TERMINAL BLOCK PLUG STACK SPCL MK COLOR
 TE Part # 1546109-4 EUROSTYLE TB,HEADER,GREY,4 POS	 TE Part # 3-284041-0 TRML BLOK VT PLUG ST 8 POS SPL PRINT	 TE Part # 3-284041-3 TRMNL BLOK VT PLUG ST 4 POS SPL PRINT	

Customers Also Bought



TE Part #796634-4
4 POS 5.08MM R/A PLUG, TRM BLK

TE Part #796634-8
8 POS 5.08MM R/A PLUG, TRM BLK

TE Part #794204-1
15P MINI UMN L2 PLUG HSG UL94V0

TE Part #796638-8
8POS 5.08MM CE R/A HDR, TRM BLK

TE Part #2-1879208-2
CPF 0402 75R 0.1% 25PPM 1K RL

TE Part #2-1825138-5
A201SYCQ04

TE Part #2143451-1
SFP+ 1X2 Assy, Sldr Tail, Tray

TE Part #1379114-2
12pos MQS .63 header 180deg

TE Part #524542-E
MSPEED 26 F SMD * 90E AB VV 137 094 **

TE Part #TRM-433-LT
Module LT 433MHz AM OOK XCVR

Documents

Product Drawings

4POS 5.08MM CE R/A HDR, TRM BLK

English

CAD Files

Customer View Model

ENG_CVM_796638-4_C3.3d_igs.zip

English

Customer View Model

ENG_CVM_796638-4_C3.3d_stp.zip

English

Customer View Model

ENG_CVM_796638-4_C3.2d_dxf.zip

English

3D PDF

English

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_796638-4_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_796638-4_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_796638-4_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Eurostyle Terminal Blocks Focus Product Stock List](#)

English

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)

English

[BUCHANAN PCB TERMINAL BLOCKS](#)

English

[1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English