★ 100% EAS Guaranteed
★ Green Device Available
★ Super Low Gate Charge
★ Excellent CdV/dt effect decline
★ Advanced high cell density Trench technology

Product Summary

Green


BVDSS	RDSON	ID
60V	12mΩ	50A


Description

The **XR50N06F** is the high performance complementary N-ch MOSFETs with high cell density, whichprovide excellent RDSON and gate charge for most of the synchronous buck converter applications .

The **XR50N06F** meet the RoHS and Green Product requirement 100% EAS guaranteed with full function reliability approved.

PDFN5060-8L Pin Configuration





Absolute Maximum Ratings (T_C=25℃ unless otherwise specified)

Symbol	Parameter		Max.	Units
V_{DSS}	Drain-Source Voltage		60	V
V_{GSS}	Gate-Source Voltage		±20	V
I_D	Continuous Drain Current	T_C = 25℃	50	A
		T_C = 100℃	33	A
I_{DM}	Pulsed Drain Current note1		200	A
EAS	Single Pulsed Avalanche Energy note2		68	mJ
P_D	Power Dissipation	T_C = 25℃	87.7	W
$R_{\theta JC}$	Thermal Resistance, Junction to Case		1.6	℃/W
T_J, T_{STG}	Operating and Storage Temperature Range		-55 to +175	℃

Electrical Characteristics (T_J=25℃ unless otherwise specified)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units
Off Characteristic						
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	V_{GS}=0V, I_D=250μA	60	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS}=60V, V_{GS}=0V,	-	-	1.0	μA
I_{GSS}	Gate to Body Leakage Current	V_{DS}=0V, V_{GS}= ±20V	-	-	±100	nA
On Characteristics						
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS}=V_{GS}, I_D=250μA	1.0	1.4	2.2	V
$R_{DS(on)}$	Static Drain-Source on-Resistance note3	V_{GS}=10V, I_D=30A	-	11	17	mΩ
		V_{GS}=4.5V, I_D=20A	-	13	22	
Dynamic Characteristics						
C_{iss}	Input Capacitance	V_{DS}=25V, V_{GS}=0V, f=1.0MHz	-	2900	-	pF
C_{oss}	Output Capacitance		-	140	-	pF
C_{rss}	Reverse Transfer Capacitance		-	120	-	pF
Q_g	Total Gate Charge	V_{DS}=30V, I_D=30A, V_{GS}=10V	-	50	-	nC
Q_{gs}	Gate-Source Charge		-	6	-	nC
Q_{gd}	Gate-Drain(“Miller”) Charge		-	15	-	nC
Switching Characteristics						
$t_{d(on)}$	Turn-on Delay Time	V_{DS}=30V, I_D=30A, R_G=1.8Ω, V_{GS}=10V	-	7.4	-	ns
t_r	Turn-on Rise Time		-	5.1	-	ns
$t_{d(off)}$	Turn-off Delay Time		-	28.2	-	ns
t_f	Turn-off Fall Time		-	5.5	-	ns
Drain-Source Diode Characteristics and Maximum Ratings						
I_S	Maximum Continuous Drain to Source Diode Forward Current		-	-	50	A
I_{SM}	Maximum Pulsed Drain to Source Diode Forward Current		-	-	200	A
V_{SD}	Drain to Source Diode Forward Voltage	V_{GS}=0V, I_S=30A	-	-	1.2	V
trr	Body Diode Reverse Recovery Time	I_F=30A, dI/dt=100A/μs	-	28	-	ns
Qrr	Body Diode Reverse Recovery Charge		-	40	-	nC

Notes:1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature

2. EAS condition : T_J=25℃,V_{DD}=30V,V_G=10V,L=0.5mH,Rg=25Ω,I_{AS}=16A

3. Pulse Test: Pulse Width≤300μs, Duty Cycle≤0.5%

Typical Performance Characteristics

Figure1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics




Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Case Temperature






Figure.11: Maximum Effective Transient Thermal Impedance, Junction-to-Case



Package Mechanical Data-PDFN5060-8L-Single



Symbol	Common			
	mm		Inch	
	Mim	Max	Min	Max
A	1.03	1.17	0.0406	0.0461
b	0.34	0.48	0.0134	0.0189
c	0.824	0.0970	0.0324	0.082
D	4.80	5.40	0.1890	0.2126
D1	4.11	4.31	0.1618	0.1697
D2	4.80	5.00	0.1890	0.1969
E	5.95	6.15	0.2343	0.2421
E1	5.65	5.85	0.2224	0.2303
E2	1.60	/	0.0630	/
e	1.27 BSC		0.05 BSC	
L	0.05	0.25	0.0020	0.0098
L1	0.38	0.50	0.0150	0.0197
L2	0.38	0.50	0.0150	0.0197
H	3.30	3.50	0.1299	0.1378
I	/	0.18	/	0.0070