










REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTE:
1.MATERIAL:
1.1 INSULATOR: HIGH TEMPERATURE PLASTIC UL 94V-0;
1.2 CONTACT: COPPER ALLOY
1.3 SHELL:STAINLESS STEEL
2.ELECTRICAL CHARACTERISTICS;
2.1 CONTACT RESISTANCE: 40mΩ Max FOR INITIAL. 30mΩ CHANGE AFTER TEST. MEASURE AT 20mV, 100mA.
2.2 CONTACT CURRENT RATING: 5A FOR VBUS PIN; 1.25A FOR VCONN PIN.
2.3 DIELECTRIC WITHSTANDING VOLTAGE: 100V AC R.M.S.
2.4 INSULATION RESISTANCE 100MΩ Min
2.5 OPERATING TEMPERATURE: -40°C ~ 85°C
3 MECHANICAL CHARACTERISTICS:
3.1 MATING FORCE: 5~20 N.
3.2 UNMATED FORCE: 8~20N AFTER TEST
3.3 DURABILITY: 10,000 CYCLES
4.PLATING
4.1 TERMINAL CONTACT: (SEE TAB) GOLD PLATING ALL OVER 50u" Min NICKEL AND 80u"Min Tin ALL OVER 50u" Min NICKEL ON SOLDER AREA
4.2 SHELL: 50u" Min. NICKEL ALL OVER,
5.TID 5719
6. "Δ" Focus on size control



PIN ASSIGNMENT:

Pin No.	Signal Name	Pin No.	Signal Name
A1	CND	B12	CND
A2		B11	
A3		B10	
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	D+	B7	D-
A7	D-	B6	D+
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10		B3	
A11		B2	
A12	CND	B1	CND

UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS: ANGLES:		TITLE	TYPE C板上单排16PIN L=9.50mm无弹片			
X :±0.50	X :±2°	DWN	xiong	PART NO. MC-121-L95		
X.X :±0.30	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
		CUSTOMER COPY				




REV.	ECN NO OR DESCRIPTION	REVISED	DATE




① 产品入载带示意图

② 卷盘贴标签示意图

③ 7盘产品叠层示意图



⑤ 外箱封箱示意图



④ 产品入外箱示意图

	REEL	CARTON
CONNECTOR (PCS)	900	6300

包装说明:

1. 将检验好的成品,对插口朝前放入载带,每卷装900PCS产品;具体如图一所示
2. 将包装好的产品,每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每7盘叠;具体如图三所示
5. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
(产品包装的标签,如客户有要求,请按客户要求包装出货)
6. 载带前面留18PCS空格,后面留18PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
剥离角度:165°-180°

UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS: ANGLES:		TITLE	TYPE C板上单排16PIN L=9.50mm无弹片			
X :±0.50	X :±2°	DWN	xiong	PART NO. MC-121-L95		
X.X :±0.30	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4
CUSTOMER COPY						