


修 订	标 记	修 改 描 要	签 名	日 期
REV NO		REVISON DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12




- NOTE:
- MATERIAL
    - HOUSING: LCP ;COLOR:BLACK; UL94V-0
    - CONTACT: COPPER ALLOY
    - SHELL: SUS 304 T=0.20
  - FINISH:
 

CONTACT:


    - GOLD PLATING ON CONTACT AREA.
    - 80u" SN PLATING ON SOLDER TAIL AREA,
    - 50u" MIN. NICKEL UNDERPLATING OVERALL,
  - ELECTRICAL:
    - VOLTAGE RATING: 30VAC RMS;
    - CURRENT RATING: 2.0 A(pin1,5);1.0A(pin2,3,4)
    - CONTACT RESISTANCE: 50 MILLIOHMS MAX;
    - INSULATION RESISTANCE: 100MEGOHMS MIN
    - DIELECTRIC WITHSTANDING VOLTAGE:500V AC FOR 1MINUTE
  - MECHANICAL:
    - OPERATING LIFE:5000YCKES
  - ENVIRONMENTAL:
    - OPERATING TEMPERATURE: -20°C TO 85°C.

RECOMMENDED PCB LAYOUT




Pin Assignments

Contact No.	Signal Name
1	VBUS
2	D-
3	D+
4	ID
5	GND
SHELL	Shield





深圳市华德共创科技有限公司  
Shenzhen Huade co-create Technology Co., LTD  
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 	TITLE: 产品名称: MICRO公头沉板编带					
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: MICRO-ZD-102PWB			
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001

由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作