

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

LOC	DIST
HM	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	U	REVISED PER ECO–15–007385	20MAY2015	GG	LS





1. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.

2. MATERIAL: HOUSING– POLYCARBONATE, BLUE
TERMINAL– .36 [.014] THICK PHOSPHOR BRONZE PLATED WITH .178µm [.000007] THICK GOLD IN LOCALIZED PLATE AREA OVER .762µm [.000030] THICK PALLADIUM NICKEL IN LOCALIZED PLATE AREA OVER 2.54µm [.000100] THICK NICKEL ON ENTIRE CONTACT.
SHIELD– COPPER ALLOY WITH 1.27µm [.000050] MINIMUM SEMI–BRIGHT (SATIN) NICKEL.

3. PLUG WILL ACCEPT 24 OR 26 AWG SOLID WIRE HAVING A MAXIMUM INSULATION DIAMETER OF 0.89–0.99[.035–.039] AND A MAXIMUM OVAL CABLE JACKET OF 2.54 X 8.89[.100 X .350].

4. TERMINATED DIMENSION 6.15[.242] MAXIMUM.

6. 10,000 ASSEMBLIES PER PACKAGE.

7. 500 ASSEMBLIES PER PACKAGE.

8. 100 ASSEMBLIES PER PACKAGE.

10. REELED PRODUCT ON STRIP DOES NOT HAVE VOID CORING ILLUSTRATED ON THIS DRAWING.

11. 100 ASSEMBLIES PER CARTON.

554720

SUPERSEDED BY: 5-554720-2

OBSOLETE

PACKAGED	PART NO.
REELED 10	554720–1
11	3–554720–3
6	5–554720–1
7	5–554720–2
8	5–554720–3

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED: 1

0 PLC	± –
1 PLC	± –
2 PLC	± –
3 PLC	± –
4 PLC	± –
ANGLES	± –

MATERIAL – 2

FINISH – 2

DWN	L. HALL	03NOV2005
CHK	C. CASH	03NOV2005
APVD	C. CASH	03NOV2005

PRODUCT SPEC 108–1163

APPLICATION SPEC 114–6016

WEIGHT –

TE Connectivity

NAME MODULAR PLUG ASSEMBLY, 8 POSITION, SOLID WIRE –

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C–554720	–

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV U