


SIGN	DATE	DESCRIPTION	APPROVER
1	01/24'07	The Soldering temperature from 245° to 250°	Aaron
2	01/24'07	Add "VDE" stipulation	Aaron
3	01/02'13	change the electrical specification and the dimension from 3.6 to 3.3	Da cheng
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	







Material

- Item ① Contact pin : Brass.Tin plated
- Item ② Wire guard: Stainless steel
- Item ③ Insulator body: Thermoplastic (UL94V-0)
- Item ④ Pad board: Thermoplastic (UL94V-0)
- Item ⑤ Insulating cover :Thermoplastic (UL94V-0)

Electrica

	cULus	VDE
Voltage rating:	300VAC	450VAC
Current rating:	10A	6A
Wire range:	0.5mm²	
Solid wire(AWG):	14-20	
Stranded wire(AWG):	14-20	
Wire strip length:	9-10mm	
Withstanding Voltage:	1.6KV	2.5KV
Operating temperature:	-40°C to +115°C	
Soldering temperature:	260°C±5°C/5 Sec	
Safety Approval:		
Critical dimension:		


HB x x 1 1 x 1 xxxx G

RoHs compliant (lead<4%) In copper Alloy

No. OF POLES
02: 2 POLES
03: 3 POLES
:
:
12: 12 POLES

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

000 0 Standard @ Logo
000 A Standard ANY Logo
Any special item by customer request, please contact sales department.



P.C.B. LAYOUT
Top view

N=NUMBER OF POLES

Dim L	(N-1)×10.0+6.0
Dim B	(N-1)×10.0

	Dim L	Dim B
2-4p	±0.25	±0.15
5-8p	±0.35	±0.25
9-12p	±0.45	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HB - 10.0mm Series (single wire w/o lever)				
PART NO.	HBxx11x1xxxxG			DWG NO.	8HB0203
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Da cheng 2013.01.02	Da cheng 2013.01.02	SHEET: 01/01	UNIT: mm / SCALE: NONE / REV.: F

Tolerance: X. ±0.50, X.X ±0.30, X.XX ±0.10, X° ±1°