

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST
-	-


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ADD DIMENSION AS MARKED	17DEC15	N.W	X.X
	A3	CHANGE PRODUCT SPECIFICATION	17SEP18	T.F	C.W







ITEM	MATERIAL	FINISH
1	COPPER ALLOY	NICKEL UNDER PLATED ALL OVER CONTACT AREA:Au(0.3um,0.76um) SOLDER TINE AREA:TIN PLATE
2	ZINC	NICKEL PLATING
3	STEEL T=0.25	NICKEL PLATE OVER COPPER UNDERPLATE
4 5	THERMO-PLASTIC UL:94V-0	COLOR:BLACK
6	COPPER ALLOY	TIN PLATE OVER NICKEL UNDERPLATE




SECTION A-A
SCALE 4:1




NOTES:
1. RECOMMENDED SCREW SIZE:M2.6 PANHEAD SCREW(L=5)
2. RECOMMENDED PCB THICKNESS:1.6MM(REF.)
A3 3. RECOMMENDED THE SCREW TORQUE 0.25~0.35N-m






FOR 20,36 POSITION
RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE: ±0.05



FOR 26,50 POSITION
RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE: ±0.05



RECOMMENDED PANEL CUTOUT
THK, 2MM MAX.

F	E	D	C	B	A	Au PLT.	POS. N	PN
42.8	42.50	52.40	46.50	35.48	30.48	0.76um	50	5-2271101-2
33.9	33.61	43.51	37.61	26.59	21.59	0.76um	36	4-2271101-2
27.6	27.26	37.16	31.26	20.24	15.24	0.76um	26	3-2271101-2
23.8	23.45	33.35	27.45	16.43	16.43	0.76um	20	2-2271101-2
							14	
42.8	42.50	52.40	46.50	35.48	30.48	0.3um	50	5-2271101-1
33.9	33.61	43.51	37.61	26.59	21.59	0.3um	36	4-2271101-1
27.6	27.26	37.16	31.26	20.24	15.24	0.3um	26	3-2271101-1
23.8	23.45	33.35	27.45	16.43	11.43	0.3um	20	2-2271101-1
							14	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.2
1 PLC ±0.2
2 PLC ±0.2
3 PLC ±0.2
4 PLC ±-
ANGLES ±2°

MATERIAL -
FINISH -

DWN HAO WANG 07AUG13
CHK KOBBY ZHAO 07AUG13
APVD XIANG XU 07AUG13
PRODUCT SPEC 108-137364 A3
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME SCSI .050 RECEPTACEL HDR ASSY -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2271101	-

Customer Drawing | SCALE 1:1 | SHEET 1 OF 1 | REV A3