


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2025.09.11	




FRONT VIEW




RIGHT SIDE VIEW





BOTTOM VIEW



RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE

X12ADIWA6SBX133

1:Au=1U"
3:Au=3U"
4:Au=6U"
5:Au=15U"
6:Au=30U"

MATERIAL :
HOUSING : LCP,UL94V-0,BLACK.
TERMINAL : PHOSPHOR BRONZE T=0.35MM,
GOLD PLATING
MECHANICAL :
DURABILITY : 750 CYCLES MIN,12.5MM/MINUTE.
INSERTION FORCE :2.2KG.F MAX
RETENTION STRENGTH :7.7KG.F BETWEEN JACK AND PLUG.
OPERATING TEMPERATURE : -40°C~+85°C.
STORAGE TEMPERATURE : -40°C~+85°C.
ALL CRITICAL DIMENSIONS WITH "*"
ELECTRICAL :
VOLTAGE : 125 VOLTS AC.
CURRENT RATING : 1.5AMP.
DIELECTRIC STRENGTH : 1000 VAC RMS 50HZ OR 60HZ,1 MIN
INSULATION RESISTANCE : 500 MEGA OHMS MIN.INITIAL
AFTER 500V DC FOR 1 MINUTE.
CONTACT RESISTANCE :SINGLE TERMINAL 30 MILLIOHMS MAX.
INITIAL 50 MILLIOHMS MAX. AFTER
DURABILITY TEST.

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	

XKB Connection

DESIGN		VIEW:	MODEL TYPE: RJ JACK
CHECKED		UNIT: mm/in	PART NO.: X12ADIWA6SB1133
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn