





RoHS Compliant



- NOTE:
- MATERIAL:
    - HOUSING:PBT, COLOR:BLUE.
    - TERMINAL:COPPER ALLOY.
    - SHELL:SPCC
    - SCREW:SPCC
    - GROUNDING:SPCC
  - PLATING:
    - CONTACT: CONTACT: 80u" Min. TIN PLATED OVERALL  
50u" Min. NICKEL UNDER-PLATED
    - SHELL:50u" Min, NICKEL PLATED OVERALL
    - GROUNDING:50u" Min, TIN PLATED OVERALL.
    - SCREW:50u" Min, NICKEL PLATED OVERALL.
  - SPECIFICATIONS:
 

VOLTAGE: 500 VAC(RMS) MAX.  
 CURRENT RATING: 3 AMPERE PER CONTACT  
 CONTACT RESISTANCE: 25 MILLIOHMS MAX.  
 INSULATION RESISTANCE: 1000 MEGOHMS MIN.  
 DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC(RMS)  
 VGA TOTAL MATING FORCE: 6.0 KGF MAX.  
 VGA TOTAL UNMATING FORCE: 1.0 KGF MIN.  
 MATING FORCE: 5.1Kg.Max.  
 UNMATING FORCE: 1.0Kg MIN.  
 OPERATING TEMPERATURE:-25°C ~ +85°C

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	HDR3.08 母座直锁式		
		料号 (PART NO)	MLD-HDR15PF-3.08		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次 (REV): A/0	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X' ± 5' X.X' ± 2'	模号 (MODEL NO)	审核 (CHECKED)		邱敏
		图号 (DWG NO)	MLD-2509031032	核准 (APPROVED)	陈镇