



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

技术要求 Specification:

1. 材质 Material: PA66 UL94V-0:
2. 额定电流 Current rating: 2.0A AC, DC
3. 额定电压 Voltage rating: 100V AC, DC
4. 温度范围 Temperature range: -25°C to +85°C
5. 接触电阻 Contact resistance: $\leq 20m\Omega$
6. 绝缘电阻 Insulation resistance: $\geq 1000M\Omega$
7. 耐压 Withstand voltage: 800V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

Part No	Pin	A	B	C
CPHR-2N-JK	2	2.00	5.70	4.50
CPHR-3N-JK	3	4.00	7.70	6.50
CPHR-4N-JK	4	6.00	9.70	8.50
CPHR-5N-JK	5	8.00	11.70	10.50
CPHR-6N-JK	6	10.00	13.70	12.50
CPHR-7N-JK	7	12.00	15.70	14.50
CPHR-8N-JK	8	14.00	17.70	16.50
CPHR-9N-JK	9	16.00	19.70	18.50
CPHR-10N-JK	10	18.00	21.70	20.50
CPHR-11N-JK	11	20.00	23.70	22.50
CPHR-12N-JK	12	22.00	25.70	24.50
CPHR-13N-JK	13	24.00	27.70	26.50
CPHR-14N-JK	14	26.00	29.70	28.50
CPHR-15N-JK	15	28.00	31.70	30.50
CPHR-16N-JK	16	30.00	33.70	32.50

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±1*	PART NO.	TITLE:	
.XX ±0.20		CPHR-XN-JK	PH2.0MM HOUSING	
.XXX ±0.10		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	---	APPD: Ava		
FINISH	---		SCALE N:A SHEET 1/1	