由 Autodesk 教育版产品制作

Features:
1. 2~8 circuits available;
2. Material:LCP UL94V-0 Black/Natual;
3. PIN Material:High conductivity copper alloy Tin-plated or Gold-plated,SQ0.64;
4. Mates with H350S12 housing;

Specification:
Current rating:14A at 16A.
Voltage rating:400V AC(RMS) or 400V DC Max.
Contact resistance:10mΩ Max.
Insulation resistance:100MΩ Min.
Withstanding voltage:1800VAC/minute.
Ambient temperature range:-40°C~105°C.

Dimensional infotmation(mm)

Circuits	DIM A	DIM B	DIM C
2	3.50	8.00	
3	7.00	11.50	
4	10.50	15.00	7.00
5	14.00	18.50	10.50
6	17.50	22.00	14.00
7	21.00	25.50	17.50
8	24.50	29.00	21.00


H3500S14-XX-XX-X


SERIES NO:

PIN Q'PY:
02~08


PLATING:
0T-Tin-plated
G1-Gold/Tin

A-BLACK (A KEY)
B-NATURE (B KEY)








PCB layout





PCB layout(3P)











KEY B






KEY A



REV	Description	DATE	GENERAL TOLERANCES (unless specified)	UNITS	MM	DATE	2019-03-05	连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS(SHENZHEN)CO.,LTD	
A	新版发行	2019-06-05	X.X±0.4	SCALE	1:1	DRAWING	Liu zhi guo		
			X.XX±0.25	REV	A	CHECKED BY	Li peng	PRODUCT NAME	3.5 mm Right Angle header
			X.XXX±0.15			APPROVAL BY	OYSW	RART NUMBER	H3500S14-XX-XX-X

由 Autodesk 教育版产品制作