



# 承認書

## SPECIFICATION FOR APPROVAL

CUSTOMER:

DESCRIPTION:

WIRE WOUND CHIP INDUCTOR

PART NO:

MWI1008PS系列

CUST. PART NO:

REV. NO.

A0

DRAWING		
PREPARED	CHECKED	APPROVED
邹声平	卢嘉良	曾凡强
DATE:	2025/5/1	

CUSTOMER APPROVE



**东莞市铭易轩电子科技有限公司**

DongGuan Ming Yixuan Electronic Technology Co., LTD


地址: 广东省东莞市大朗镇景泰路20号VV大厦

电话: 15970768093 , 13640935893

网址: <http://www.dgmingyixuan.com>




CUSTOMER:		REV. NO.	A0
PART NO:	MWI1008PS系列	PAGE NO:	2/6
CUST. PART NO:		DATE:	2025/5/1

**1. SHAPE & DIMENSION (UNIT:mm)**


Recommended patterns

L	W	T	E	F	D
3.81 Max.	3.81 Max.	2.74 Max.	1.02 Typ.	2.54 Typ.	1.27 Typ.

**2. SCHEMATIC**

**3. PART NUMBERING SYSTEM**

MWI	1008	PS	1R0	M	S	T	-	LF
1	2	3	4	5	6	7		8

1 PRODUCT SYMBOL (产品代号)

2 DIMENSIONS (规格尺寸)

3 MATERIAL (芯片类型)

4 INDUCTANCE (电感量)

5 TOLERANCE (公差) : M±20%

6 TERMINAL (端电极材料) : S-锡端头;

7 PACKAGING (包装方式) : T-编带盘装; B-散装

8 E.P. (环保) : LF—Lead Free HF—Halogen Free FP—Red Phosphor Free

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO:	A0
PART NO:	MWI1008PS系列	PAGE NO:	3/6
CUST. PART NO:		DATE:	2025/5/1

**4. ELECTRICAL CHARACTERISTICS**

No.	Part Number	L	Freq	Q@1MHz	SRF	Rdc	Isat
		( $\mu$ H)	(KHz/V)	Min.	(MHz)Min.	( $\Omega$ ) Max.	(A)Max.
1	MWI1008PS1R0MST-HF	1	100/0.1	22	254	0.06	3.00
2	MWI1008PS1R5MST-HF	1.5	100/0.1	22	220	0.10	2.50
3	MWI1008PS2R2MST-HF	2.2	100/0.1	25	200	0.12	2.40
4	MWI1008PS2R7MST-HF	2.7	100/0.1	22	150	0.22	1.70
5	MWI1008PS3R3MST-HF	3.3	100/0.1	25	150	0.35	1.50
6	MWI1008PS3R9MST-HF	3.9	100/0.1	22	150	0.30	1.50
7	MWI1008PS4R7MST-HF	4.7	100/0.1	22	120	0.35	1.20
8	MWI1008PS5R6MST-HF	5.6	100/0.1	25	100	0.36	1.30
9	MWI1008PS6R8MST-HF	6.8	100/0.1	25	100	0.58	1.30
10	MWI1008PS100MST-HF	10	100/0.1	25	105	0.92	0.84
11	MWI1008PS150MST-HF	15	100/0.1	25	35	1.15	0.81
12	MWI1008PS220MST-HF	22	100/0.1	25	25	1.40	0.67
13	MWI1008PS330MST-HF	33	100/0.1	25	20	1.61	0.53
14	MWI1008PS390MST-HF	39	100/0.1	25	16	1.85	0.49
15	MWI1008PS470MST-HF	47	100/0.1	25	19	2.50	0.47
16	MWI1008PS680MST-HF	68	100/0.1	25	12	3.80	0.42
17	MWI1008PS820MST-HF	82	100/0.1	25	9	4.30	0.33
18	MWI1008PS101MST-HF	100	100/0.1	25	7	6.50	0.35
19	MWI1008PS121MST-HF	120	100/0.1	25	7	7.00	0.30
20	MWI1008PS151MST-HF	150	100/0.1	25	5	7.50	0.27
21	MWI1008PS221MST-HF	220	100/0.1	25	4	10.00	0.21
22	MWI1008PS331MST-HF	330	100/0.1	25	3	11.50	0.19

产品公差: M $\pm$ 20%

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平



CUSTOMER:		REV. NO:	A0
PART NO:	MWI1008PS系列	PAGE NO:	4/6
CUST. PART NO:		DATE:	2025/5/1

#### 4. ELECTRICAL CHARACTERISTICS

No.	Part Number	L	Freq	Q@1MHz	SRF	Rdc	Isat
		( $\mu$ H)	(KHz/V)	(Typ.)	(MHz)Min.	( $\Omega$ ) Max.	(A)Max.
23	MWI1008PS471MST-HF	470	100/0.1	23	3	16.3	0.14
24	MWI1008PS681MST-HF	680	100/0.1	18	2	24.0	0.11
25	MWI1008PS821MST-HF	820	100/0.1	18	2	26.0	0.10
26	MWI1008PS102MST-HF	1000	100/0.1	18	2	29.0	0.11

产品公差: M $\pm$ 20%

#### Test remarks


- (1). All test data is referenced to 25 °C ambient.
- (2). Isat: DC current at which inductance drops approximate 30% from its value without current,

#### 5. GENERAL SPECIFICATION

- (1). Operating temp.: -40°C ~ + 85°C (Including self-generated heat).
- (2). Storage temp.: -10°C ~ +40°C R.H.:60% Max.
- (3). Moisture sensitivity level (MSL) 1
- (4). Recommended products should be used within 12 months from the date of delivery
- (5). The part temperature (ambient + temp rise) should not exceed 85 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI1008PS系列	PAGE NO:	5/6
CUST. PART NO:		DATE:	2025/5/1

**6. SOLDERING CONDITIONS**
**Figure 1. Re-flow Soldering (Lead Free)**



Note:

Preheat circuit and products to 150°C

260°C tip temperature (Max)

Reflow times: no more than 2 times

Solder paste thickness: the best 0.08mm is ,but max is 0.1mm

**Figure 2. Hand Soldering**


Note:

Use a 20 watt soldering iron with tip diameter of 1.0mm

Limit soldering time to 3 sec.


APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV NO:	A0
PART NO:	MWI1008PS系列	PAGE NO:	6/6
CUST. PART NO:		DATE:	2025/5/1

7. PACKAGING(unit: mm)

1.包装类型: 编带装

2.包装尺寸:  13" 盘  7" 盘



Item	W	A0	B0	K0	P	T	E	F	D0	P0
DIM(mm)	12±0.3	5.4±0.15	5.4±0.15	2.4±0.1	8.0±0.1	0.35±0.05	1.75±0.1	5.5±0.1	1.5±0.1	4.0±0.1

包装数量: 2000PCS / 卷

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	谢海龙