

Shenzhen DreamLNK Technology Co., Ltd.
深圳市骏晔科技有限公司

GPS+BD Ceramic Built-in Antenna

Product Specification

Client Name		Frequency Band	1560-1572.42±3MHz
Wire Name		Version	A1
Customer's Part Number		DreamLNK's Part Number	805
RF Designer	James Wang	RF Manager	Knight Ai
Structural Designer		Structural Design Manager	
Technical Director		Date	2018-07-16


Client confirmation:

Whether the product meets your requirements? OK NG

Contents

Cover	1
Contents	2
1. Photos	3
2. Parameters	3
3. S11 Data	4
4. Structure diagram	5
5. Environmental reliability experiment report	6
6. Contact us	6

1. Photo




2. Parameters


Test parameters			
Product Name	GPS+BD Ceramic Antenna	Model No	805
Electrical Specifications			
Frequency Range	1560-1572.42 ± 3MHz	Polarization	Circular polarization
Input Impedance	50 Ω	Radiation direction	Directional
VSWR	≦ 1.5	Power Capacity	20W
Gain	4dBi	Amplifier Gain	28dBi
Mechanical Specifications			
Dimensions	25x25x8mm	Color	/
Connector Model	IPEX-1	Cable Length	1.13~150 mm
Antenna Material	Ceramic	Voltage	DC3.0~5V
Working Temperature	-40°C~+85°C	Relative Humidity	40~85%

The information provided by us should be kept strictly confidential, and it is not allowed to disclose to anyone else or other companies, without prior written consent

3. S11 Data (VSWR, Return loss, Smith)



4. Structure diagram



5. Environmental reliability experiment report

Item	Test condition	Specification
Storage environment	Tested temperature, humidity and air pressure as following without specifying: 1. The temperature is $-30\text{ }^{\circ}\text{C} \sim +80\text{ }^{\circ}\text{C}$ 2. Relative humidity is 45% -85% 3. The air pressure is 86kpa-106kpa	The electrical mechanical performance is normal
High and low temperature test	Perform 5 cycles between $70\text{ }^{\circ}\text{C}$ and $40\text{ }^{\circ}\text{C}$, then check the appearance quality, under normal conditions 1-2H	The size should meet the requirements for mechanical and electrical performance
Resistant to constant heat and humidity	Test Relative humidity: $95 \pm 3\%$, Test temperature: $40\text{ }^{\circ}\text{C}$. After continuous 2H running, take out the sample, and measure its electrical properties within 5 minutes, put the sample in a normal condition for another 1-2H, check the appearance quality	The size should meet the standard, and meet for mechanical and electrical performance
Vibration test	Vibration frequency range 10-55HZ, displacement amplitude: 0.35MM, acceleration amplitude: 50.0M / S, frequency of sweeping cycle: 30 times	Normal electrical and mechanical performance

6. Contact us

Shenzhen DreamLnk Technology Co., Ltd

★ Data collection, Smart home, Internet of Things applications, Wireless remote control technology, Remote active RFID, Antennas ★

Office Add.: Room 603, Unit C, Zone A, Huameiju Business Center, Xihu Rd., Bao'an District, Shenzhen, Guangdong Province, China

Factory Add.: 5th Floor, Building B, Huazhi Innovation Valley, No. 7 Yuhua Street, 138 Industrial Zone, Tangxia Town, Dongguan, Guangdong Province, China