




RECOMMENDED PCB LAYOUT



- Note:
- 1: Material(材料):
Barrel: Brass C3602 (针体: 黄铜 C3602)
Housing: PA46+30%GF (胶芯: PA46, 黑色).
Magnet: NdFeB (磁铁: 钕铁硼)
 - 2: Plating(电镀):
Barrel: 3u' Au over 50~80u' Ni(针体: 镀金3u', 镍底50~80u'.)
Magnet: Nickel plating (镀镍)
 - 3: Electrical(电气特性):
Insulation Resistance: 1,000MΩ minimum. (绝缘电阻: 1,000MΩ以上)
Dielectric Withstand Voltage: 500VAC/minute. (抗击电压: 500VAC/minute)
 - 5: WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: -20℃~ +70℃

