



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)



SPECIFICATIONS

Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insulator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
BX-PZ1.0-2-1PWZ	2*1	0.00	1.00
BX-PZ1.0-2-2PWZ	2*2	1.00	2.00
BX-PZ1.0-2-3PWZ	2*3	2.00	3.00
BX-PZ1.0-2-4PWZ	2*4	3.00	4.00
BX-PZ1.0-2-5PWZ	2*5	4.00	5.00
BX-PZ1.0-2-6PWZ	2*6	5.00	6.00
BX-PZ1.0-2-7PWZ	2*7	6.00	7.00
BX-PZ1.0-2-8PWZ	2*8	7.00	8.00
BX-PZ1.0-2-9PWZ	2*9	8.00	9.00
.....
BX-PZ1.0-2-40PWZ	2*40	(PIN-1)	(PIN)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA
			X.±0.30	X.*±5°		
.X±0.20	.X*±1°	核准 APPROVAL	JADE			
.XX±0.10	.XX*±0.5°			单位 UNITS	MM	比例 SCALE

料号 PART NO.	BX-PZ1.0-2-NPWZ	版本 REV.	A
品名 TITLE	1.0PH H1.0 2xPin SMT W2.3 PCS.0 PA2.0 PB1.4 LS.0 6T	页次 SHEET	1/1
客户料号 CUTM.NO.			

