

## SOD-123 Surface Mount Schottky Barrier Rectifier

### Features

- $V_R=30/40V$
- $I_{F(AV)}=0.5A$
- High Current Capability
- Low Forward Voltage Drop


### Applications

The device is a single rectifier offering low VF and excellent high temperature stability.

### Mechanical Data

- Case: SOD-123  
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity: Cathode line denotes the cathode end

### Function Diagram



**Reverse Voltage**  
30/40 V  
**Forward Current**  
0.5 Ampere

SOD-123



### Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	MBR0530	MBR0540
Maximum repetitive peak reverse voltage	$V_{RRM}$	V	30	40
Maximum RMS voltage	$V_{RMS}$	V	21	28
Maximum DC blocking voltage	$V_{DC}$	V	30	40
Maximum Average Forward Rectified Current	$I_{F(AV)}$	A	0.5	
Non-repetitive Peak Forward Surge Current @t=8.3ms Half-sine wave	$I_{FSM}$	A	5.5	
Power Dissipation	$P_D$	mW	500	
Junction temperature	$T_j$	°C	-55-+125	
Storage temperature range	$T_{STG}$	°C	-55-+150	
Typical thermal resistance	$R_{\theta J-A}$	°C /W	200	

● **Electrical Characteristics** (Ta=25°C Unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	MBR0530	MBR0540
Maximum forward voltage	I <sub>F</sub> = 0.1A	V <sub>F1</sub>	V	0.39	—
	I <sub>F</sub> = 0.5A	V <sub>F2</sub>		0.47	0.51
	I <sub>F</sub> = 1.0A	V <sub>F3</sub>		—	0.62
Maximum reverse current	V <sub>R</sub> = 10V	I <sub>R</sub>	μA	—	—
	V <sub>R</sub> = 15V			20	—
	V <sub>R</sub> = 20V			—	10
	V <sub>R</sub> = 30V			130	—
	V <sub>R</sub> = 40V			—	20
Capacitance between terminals	V <sub>R</sub> = 0V, f = 1MHz	C <sub>T</sub>	pF	170	

● **Ratings And Characteristics Curves** (Ta=25°C Unless otherwise specified)




Fig.1 Typical Instantaneous Forward Characteristics




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Junction Capacitance




Fig.4 Power Derating Curve

# MBR0530 THRU MBR0540

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

## ● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOD-123	R1	0.012	3000	45000	180000	7"

## ● Package Outline Dimensions (SOD-123)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	3.55	3.85	0.140	0.152
B	2.55	2.85	0.100	0.112
C	1.40	1.80	0.055	0.071
D	0.95	1.35	0.140	0.152
E	0.51	0.71	0.037	0.053
F	-	0.15	-	0.006
G	0.15	0.45	0.006	0.008
H	0.08	0.25	0.003	0.010
$\theta$	-	8°	-	8°

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	0.91	-	0.036	-
K	-	2.36	-	0.092
M	1.22	-	0.048	-