

DASH No. ダッシュ 番号	POSITION 位置 指数	A	B	C	D	E	F	G
171229-1	20	13.3	11.3	9.9	42.3	40.3	38.1	20.4
↑	-2	26	16.3	14.1	13.1	44.2	42.2	40.8
	-3	34	21.2	19.0	17.2	53.7	51.7	49.7
	-4	50	21.2	18.9	17.2	68.8	66.8	64.8
↓	-5	75	30.3	28.2	26.3	68.8	66.8	64.8
	-6	70.4	10.9	38.5	36.9	72.4	70.4	68.4
		10.4 (CRAFT PASTED)	30.6	28.6	26.2	74.4	72.4	70.8

NOTE: ~~171229-7~~ ~~10.4 (CRAFT PASTED)~~ ~~30.6~~ ~~28.6~~ ~~26.2~~ ~~74.4~~ ~~72.4~~ ~~70.8~~ ~~35.8~~


注. ~~セーラーファスナー型は使用できない~~ NOTES;

△ 軽度の内側への変形は許される。 △ A SLIGHT DEFORMATION TO INSIDE IS PERMISSIBLE.

3. 取扱説明書(15-025J)参照。

3. REFER TO INSTRUCTION SHEET (15-025J).

底部表側に AMP マーク
STAMP "AMP" MARK ON THE SURFACE.




[一般公差 ±0.6]

[GENERAL TOLERANCE ±0.6]

△ 171229-2 は 353044-1 に置換する。

△ 171229-2 TO BE SUPERSEDED BY 353044-1.

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



E	-2 SUPERSEDED	Y.I	S.M	3/4/96
D ₂	OBSOLETE-7 (F398-1/182-94)	K.N	S.M	12-26/94
D ₁	OBSOLETE-6 (F398-0539)	K.I	Y.T	7-23/93
D	REVISED	K.S	Y.T	8-14/94
C ₁	REACTIVE	K.S	Y.T	7-23/93
C	REVISED	Y.T		5-22/93
B	REVISED (P-DWG REV-A)	Y.O	Y.S	4/8/93
A	REVISED (P-DWG REV-A)	Y.O	Y.S	4/8/93

E1 REV PER ECO-10-000445 KK HMR JAN10

1972 by AMP (Japan), Ltd. ALL RIGHTS RESERVED AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING

参考図面
(CUSTOMER COPY
REFERENCE ONLY)

MATERIAL: POLYPROPYLENE (BLACK)
色: 黒色 (黒色)

AMP

AMP (JAPAN), LTD.
Tokyo, Japan

適合電線断面積 WIRE RANGE

分類 (CLASS)

mm²/AWG

実用外径 (INSULATION DIA.)

タイプ (TYPE)

mm (IN.)

公差 (TOLERANCE)

尺貫 SCALE

LOC

SIZE

番号 (NO.)

REV

EXCEPT (0.4 (0.015) AS NOTED)

2-1

J

AC

171229

E1

名称 (NAME): DUST COVER AMP-INCERT "M" SERIES BLOCK

ペン 1 1/2 インチ "M" シリーズ用 ダストカバー