

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- - -

LOC

DIST

REVISIONS

C

COPYRIGHT 2011 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

DW

P	LTR	DESCRIPTION	DATE	DWN	APVD
E1		REVISED (ECR-14-000556), ADD NEW PART NUMBER.	06JAN14	S.C.	H.L.

NOTES:

1. MATERIAL:

1.1 HOUSING: THERMOPLASTIC (PA9T)
UL94 V-0, COLOR: BLACK.1.2 ACTUATOR: THERMOPLASTIC (PA9T)
UL94 V-0, COLOR: BLACK.

1.3 CONTACTS: PHOSPHOR BRONZE

1.4 MYLAR: CAPTON. THICKNESS: 0.12. COLOR: YELLOW

2. FINISH:

2.1 CONTACT:









GOLD FLASH PLATING OVERALL.

1.27mm (50m") MIN. NICKEL UNDERPLATING OVERALL.

3. REFLOW SOLDER CAPABLE TO 260°C PER TEC-109-201, CONDITION B.

4. WITHOUT DATE CODE FOR 8 POSITION UNDER.

5. MYLAR ATTACHED FOR PN 6-1734248-0 ONLY

RECOMMENDED PCB LAYOUT
(TOLERANCE : ±0.05)APPLICABLE FPC
RECOMMENDED DIMENSION
(THICKNESS:0.3±0.05)W/ MYLAR
4 (FOR 6-1734248-0 ONLY)

SECTION X-X

ACTIVE	27	31.40	35.6	29.0	30	6-1734248-0
OBSOLETE	37	41.40	45.6	39.0	40	4-1734248-0
	36	40.40	44.6	38.0	39	3-1734248-9
	35	39.40	43.6	37.0	38	3-1734248-8
	34	38.40	42.6	36.0	37	3-1734248-7
	33	37.40	41.6	35.0	36	3-1734248-6
	32	36.40	40.6	34.0	35	3-1734248-5
	31	35.40	39.6	33.0	34	3-1734248-4
	30	34.40	38.6	32.0	33	3-1734248-3
	29	33.40	37.6	31.0	32	3-1734248-2
	28	32.40	36.6	30.0	31	3-1734248-1
ACTIVE	27	31.40	35.6	29.0	30	3-1734248-0
	26	30.40	34.6	28.0	29	2-1734248-9
	25	29.40	33.6	27.0	28	2-1734248-8
	24	28.40	32.6	26.0	27	2-1734248-7
	23	27.40	31.6	25.0	26	2-1734248-6
	22	26.40	30.6	24.0	25	2-1734248-5
	21	25.40	29.6	23.0	24	2-1734248-4
	20	24.40	28.6	22.0	23	2-1734248-3
	19	23.40	27.6	21.0	22	2-1734248-2
	18	22.40	26.6	20.0	21	2-1734248-1
OBSOLETE	17	21.40	25.6	19.0	20	2-1734248-0
	16	20.40	24.6	18.0	19	1-1734248-9
	15	19.40	23.6	17.0	18	1-1734248-8
	14	18.40	22.6	16.0	17	1-1734248-7
	13	17.40	21.6	15.0	16	1-1734248-6
	12	16.40	20.6	14.0	15	1-1734248-5
	11	15.40	19.6	13.0	14	1-1734248-4
	10	14.40	18.6	12.0	13	1-1734248-3
	9	13.40	17.6	11.0	12	1-1734248-2
	8	12.40	16.6	10.0	11	1-1734248-1
ACTIVE	7	11.40	15.6	9.0	10	1-1734248-0
	6	10.40	14.6	8.0	9	1734248-9
	5	9.40	13.6	7.0	8	1734248-8
	4	8.40	12.6	6.0	7	1734248-7
	3	7.40	11.6	5.0	6	1734248-6
	2	6.40	10.6	4.0	5	1734248-5
	2	5.40	9.6	3.0	4	1734248-4
	2	4.40	8.6	2.0	3	1734248-3
	STATUS	DIM D	DIM C	DIM B	DIM A	POS.
						PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 30MAR2007

H. HUANG

CHK 30MAR2007

S. HOU

APVD 30MAR2007

W.J. KE

PRODUCT SPEC

108-57080

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

1.0 MM FPC, ZIF VERTICAL, SMT TYPE

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779C=1734248

SCALE SHEET 1 OF 2 REV E1

SEE SHEET 1.

5. PEELING SPEED: 300mm/minutes.



SHEET	REV	1
-------	-----	---