160928-4 ✔ ACTIVE

FASTIN-FASTON | FASTIN-FASTON 250

TE Internal #: 160928-4

Quick Disconnect Receptacle, 20 – 17 AWG, .51 – 1.03 mm² Wire, 6.35 mm [.25 in] Tab Width, Straight, Phosphor Bronze, Tin Plating, FASTIN-FASTON 250

View on TE.com >

Terminals & Splices > Quick Disconnects







Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.03 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Termination Features

Product Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Locking Lance

Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Dimensions

Product Length	19.2 mm[.755 in]
Compatible Insulation Diameter Range	1.4 – 2.3 mm[.055 – .09 in]
Terminal Material Thickness	.33 mm[.013 in]

Wire Size	.51 – 1.03 mm²

Product Type Features

Insertion Force	Normal

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 7-2150155-7
OCEAN_2.0_SPARE_PART_KIT-080F110OV




TE Part # 2150155-2
OCEAN_2.0_Applicator-E-080F110OV-REA



TE Part # 1-1579007-4
EXTRACTION TOOL



TE Part # 4-1579007-3
EXTRACTION TOOL KIT




TE Part # 2150155-1
OCEAN_2.0_Applicator-E-080F110OV-REM



TE Part # 626094-2
FF .250 REC 0.5 /1.0 MM2 0.32X19.3 TPBR

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(207)



Insertion & Extraction Tools(2)



PCB Terminals(2)



Quick Disconnects(250)

Customers Also Bought



TE Part #925661-2
.140 DIA SOCKET



TE Part #160860-4
FF 250 REC 0.5-1.0MM2 TPPB




TE Part #3-1879027-4
YR1 0.1% 97R6



TE Part #2063490-1
SDE TAB 0.5-2.5mm2 ASSY



TE Part #335104-E
SRCBUG A 2,54 2 2 CSI 112 * K-AD B500 J



TE Part #265050-005
44A0811-8-9




TE Part #BTH1-15-10-1-C
BTH1-15-10-1-C

TE Part #K1007167
Switch guard 08-0-0-01



TE Part #544720-E
SRCBUG A 2,54 2 2 CSI 163 * K-AD B500 J



TE Part #HDC16-6-LA
DUST CAP, 6P, REC, GRY, LANYARD, HD10

Documents

Product Drawings

FF 250 REC 0.5-1.0MM2 TPPB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_160928-4_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_160928-4_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_160928-4_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Application Specification

English