






RoHS



NOTE:
 1.Rating: 24V 25mA DC
 2.Insulation Resistance: ≥100 MΩ
 3.Withstand voltage:AC 500V 1Minute
 4.Operating Force Range: 1000gf Max
 5.Mechanical Life:3,000 Cycles

| Number of digits(位数) | 1P | 2P | 3P | 4P | 5P | 6P | 7P | 8P | 9P | 10P | 12P |
|----------------------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| Cover/red 盖子/红色 | DA-01 | DA-02 | DA-03 | DA-04 | DA-05 | DA-06 | DA-07 | DA-08 | DA-09 | DA-10 | DA-12 |
| | DA-01D | DA-02D | DA-03D | DA-04D | DA-05D | DA-06D | DA-07D | DA-08D | DA-09D | DA-10D | DA-12D |
| Cover/blue 盖子/蓝色 | DA-01R | DA-02R | DA-03R | DA-04R | DA-05R | DA-06R | DA-07R | DA-08R | DA-09R | DA-10R | DA-12R |
| | DA-01L | DA-02L | DA-03L | DA-04L | DA-05L | DA-06L | DA-07L | DA-08L | DA-09L | DA-10L | DA-12L |

| | | | | | |
|-----|--------------|--------|-----|-------------------|--------------|
| Ⓔ | Terminal | | 20 | Phosphorus bronze | Gold plating |
| Ⓓ | Potting glue | | | Epoxy resin | Black |
| Ⓒ | Handle | | 10 | PBT | White |
| Ⓑ | Cover | | 1 | PBT | Red/Blue |
| Ⓐ | Base | | 1 | PBT | Black |
| NO. | Name | Number | Qty | Material | Remarks |

ZHONGDI® Zhongdi Electronic Technology Co., Ltd

| | | | |
|----------|------|-------|------------|
| design | date | name | DIP SWITCH |
| Review | date | model | DA-10R |
| Approved | date | | |

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved Tolerance not specified