

Type FSH

Fast Acting Glass Tube Fuse

Automotive Glass



www.optifuse.com (619) 593-5050

Fuse Size: 1/4" x 5/8" (6.35 x 15.9mm)

Ampere Rating: 100mA ~ 30A

Voltage Rating: 125V / 250V / 32V

Electrical Characteristics:




100%	135%	200%
Min.	Max.	Max.
4h	1h	120s

Agency Standards and Listings:



According to UL248-14

Mechanical Dimensions: Inches[mm]



Part Number	Ampere Rating	Interrupt Rating	Voltage Rating	cUL _{us}	cR _{us}	PS _{JET}		
FSH-100mA	100mA	10KA @125VAC 35A @250VAC	125V/250V	●				
FSH-125mA	125mA			●				
FSH-250mA	250mA			●				
FSH-375mA	375mA			●				
FSH-500mA	500mA			●				
FSH-600mA	600mA			●				
FSH-750mA	750mA			●				
FSH-1A	1A			●		●		
FSH-1.25A	1.25A			10KA @125VAC 100A @250VAC	125V/32V	●		●
FSH-1.5A	1.5A					●		●
FSH-1.6A	1.6A	●				●		
FSH-2A	2A	●				●		
FSH-2.5A	2.5A	●				●		
FSH-3A	3A	●				●		
FSH-3.15A	3.15A	●				●		
FSH-3.5A	3.5A	●				●		
FSH-4A	4A	2020A @125VAC 1000A @32VAC	125V/32V				●	●
FSH-5A	5A					●	●	
FSH-6A	6A	1000A @32VAC		●				
FSH-6.3A	6.3A			●				
FSH-7A	7A			●				
FSH-7.5A	7.5A			●				
FSH-8A	8A			●				
FSH-10A	10A			●				
FSH-12A	12A			100A @125VAC 1000A @32VAC	●		●	
FSH-13A	13A				●		●	
FSH-15A	15A		●			●		
FSH-16A	16A		●					
FSH-20A	20A	●						
FSH-25A	25A	●						
FSH-30A	30A	●						

Warning:



-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.

-Avoid contact of Fuse device with chemical solvent. Prolonged contact may damage the device performance.