


Feb. 1. 2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD		ANSI/TIA/EIA-568-B.2.10 CAT6a				
RATING	OPERATING TEMPERATURE RANGE	① -25 °C TO 60 °C	STORAGE TEMPERATURE RANGE	-25 °C TO 60 °C		
	VOLTAGE	125 V AC	OPERATING HUMIDITY RANGE	95 % MAX		
	CURRENT	1 A	APPLICABLE CABLE	—		
<b>SPECIFICATIONS</b>						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
<b>CONSTRUCTION</b>						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.			X	X
① THE OPERATION TEMPERATURE INCLUDES THE TEMPERATURE RISE BY CURRENT CARRYING. ② TEMPERATURE RANGE FOR A CONNECTOR UNMATED. ③ USE UNDER THE CONDITION RECOMMENDED BY A CABLE MANUFACTURE.						
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
△						
REMARK				APPROVED	YH. ENAMI	09. 06. 02
				CHECKED	YH. ENAMI	09. 06. 02
				DESIGNED	MT. ITANO	09. 06. 02
Unless otherwise specified, refer to JIS C 5402.				DRAWN	MT. ITANO	09. 06. 02
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELG4-126868-02	
<b>HRS</b>	SPECIFICATION SHEET		PART NO.	TM31P-TM-88P (02)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL222-4626-7-02	△	1/1

Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



1	POLYCARBONATE	CLEAR YELLOW						
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS	
UNITS mm			SCALE 5 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-E-00018150	DESIGNED MO. SHIMOYAMA	CHECKED KG. OKITA	DATE 20250403
<b>HRS</b> HIROSE ELECTRIC CO., LTD.	APPROVED	YH. ENAMI	20090602	DRAWING NO.	EDC3-126868-02			
	CHECKED	YH. ENAMI	20090602	PART NO.	TM31P-TM-88P(02)			
	DESIGNED	MT. ITANO	20090602	CODE NO.	CL0222-4626-7-02		1	1
	DRAWN	MT. ITANO	20090602					