







SPECIFICATION:

1.MATERIAL:

HOUSING: LCP E130i 30% G/F UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG: BRASS C2680R-H,T=0.20mm

2.FINISH:


CONTACT:1u"/3u"/5u"/15u"GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL



RECOMMENDED PCB LAYOUT
UNLESS TOLERANCE: +/ -0.05

环境要求		产品必须符合ROHS要求			制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-SATA-08-22PXTM		版本 REV.	A
3	Peg	Brass C2680		Tin/Ni Plated				X.	±0.30	X.*	±3°	审核 CHECK	LEO	品名 TITLE	SATA 7+15P 直立式SMT 带接地片		页次 SHEET	1/1
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated				X.X	±0.20	X.X*	±2°	核准 APPROVAL	JOHN	客户料号 CUTM.NO.				
1	Housing	High Temp	Black	UL 94V-0				X.XX	±0.05	X.XX*	±0.5°	单位 UNITS	MM	比例 SCALE	1:1		兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK														
1		2		3		4		5		6		7		8		9		