




HAOYU



Color	VR	IF	Recommended Operating Current	VF	
				Min	Max
Cold white	DC 5V	20mA	20mA	2.5V	4.0V
Yellow	DC 5V	20mA	20mA	1.6V	2.5V
White	DC 5V	20mA	20mA	2.5V	4.0V
Orange	DC 5V	20mA	20mA	1.6V	2.5V
Blue	DC 5V	20mA	20mA	2.5V	4.0V
Green	DC 5V	20mA	20mA	2.5V	4.0V

Circuit Diagram



PCB.layout

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		NO	DATE	REVISIONS		BY	APPD	
7	LED		1		UP TO 5mm: ±0.1	ANGULAR ±1°	1						
6	SPRING	SUS	1		ABOVE 5mm: ±0.2								
5	TERMINAL	BRASS	4	Ag-PLATED									
4	HOUSING	PA66	1	BLACK	TITLE: TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN			
3	KNOB	POM	1	WHITE	MODEL: TC-1194B-G-E-C11A-01			SCALE: 1:1		CHK'D			
2	ASTIGMATISM FILM	PC	1	WHITE	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD		
1	COVER	PC	1	CLEAR									
										PRO.AGL:		REV :A0	