

■ Specifications :




- Voltage rating: 100V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M\ \Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing : $\leq 20m\Omega$

X2016 W V-05H2- 46 SN
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
② Category : W-WAFER
③ Wedding Board Angle : V-Stright 180°
④ Row No.-Pin No.: XX-02P~20P
⑤ H2:Horse Hooves
⑥ Material : 46-PA46 94V-0
⑦ Plating Category: Sn-Bright Tin Plating;

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.00	5.00	12	22.00	26.00	25.00
03	4.00	8.00	7.00	13	24.00	28.00	27.00
04	6.00	10.00	9.00	14	26.00	30.00	29.00
05	8.00	12.00	11.00	15	28.00	32.00	31.00
06	10.00	14.00	13.00	16	30.00	34.00	33.00
07	12.00	16.00	15.00				
08	14.00	18.00	17.00				
09	16.00	20.00	19.00				
10	18.00	22.00	21.00				
11	20.00	24.00	23.00				

X2016WV-05H2-46SN	PA46 UL 94V-0	Brass	Tin-Plated	X2016H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing



P.C.B LAYOUT

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors	
DWN		VIEW:	PART NO.: X2016WV-05H2-46SN	
CHKD		UNIT: mm/in	DWG NO.: X-X2016WV-05H2-46SN	
APPD		SIZE: A4	WEIGHT	
			SHEET	REVISION
			1/1	A0

					ANGLAR	±5°
Δ x					L≤ 4	±0.2
Δ x					4<L≤ 16	±0.3
Δ x					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED