



SIGN	DATE	DESCRIPTION	APPROVER
⚠1			
⚠2			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!









Material

- Item ⓐ Insulating body: Thermoplastic (UL94V-0)
- Item ⓑ Insulating lever: Thermoplastic (UL94V-0) Orange RAL 2011/P
- Item ⓒ Spring clamp: Stainless steel Matte Tin plated.
- Item ⓓ Insulating cover : Thermoplastic (UL94V-0)
- Item ⓔ Terminal side body: Thermoplastic (UL94V-0)
- Item ⓕ Terminal Cover : Thermoplastic (UL94V-2)

Electrical: cULus

- Voltage rating: 150V
- Current rating: 2A
- Solid wire(AWG): 16-22
- Stranded wire(AWG): 16-22
- Wire strip length: 9.0-10.0mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Safety Approval:
- Critical dimension: ▽C

恩尼特克電子科技(深圳)有限公司 文管中心 2014.08.13 發行 ANYTEK INTERNATIONAL CO., LTD.

NY xx 10 x 1 xxxx G — RoHs compliant (lead<4%) in copper Alloy

No. OF POLES	Body Color	
02: 2 POLES	0	Black (RAL9005)
03: 3 POLES	2	Red (RAL3001/D)
⋮	3	Orange(RAL2011/P)
24: 24 POLES	4	Yellow(RAL1018/A)
	5	Green(RAL6018/T)
	6	Blue (RAL5015/A)
	8	Grey(RAL7004/P)
	9	White(RAL1102)
	C	Multiple colors

xxxx
0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request, please contact sales department.

N = Number of poles
Dim L=(Nx3.5)+1.5
Dim P=(N-1)x3.5

POLES	Dim L	Dim P
2p-6p	±0.15	±0.15
7p-12p	±0.2	±0.2
13p-18p	±0.3	±0.3
19p-24p	±0.4	±0.4

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NY-3.5mm Series (with cover)				
PART NO.	NYxx10x1xxxxG			DWG NO.	8NY0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Guoxue 2014.08.06	Guoxue 2014.08.06	UNIT: mm SCALE: NONE SHEET: 01/01 REV.: B	

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°