THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
AF	50


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	0	TRANSFERED TO TYCO FORMAT	18FEB03	MF	EH

1 CRIMPBAND MATERIAL PROVIDED IN CONTINUOUS STRIP.


2 REFERENCE DESCRIPTIVE PART NUMBER L125/076C18BSP.

△3 BLANK LENGTH DETERMINED BY 125/076 TOOLSET.





TYP. CROSS SECTION



PARTIAL FORMED VIEW (REF)
FORMED BY APPLICATION TOOLING

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± .005
4 PLC ± –
ANGLES ± –

MATERIAL: UNS C26000 BRASS –

FINISH: NONE

DWN	18FEB2003 MICHAEL S. FEHER
CHK	18FEB2003 EDWARD HOWARD
APVD	18FEB2003 EDWARD HOWARD
PRODUCT SPEC	–
APPLICATION SPEC	–
WEIGHT	–

CUSTOMER DRAWING

1601698–1
PART NUMBER

tyco Electronics
Tyco Electronics Corporation
Harrisburg, PA 17105–3608

NAME
–
CRIMPBAND, RTM
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1601698	–

SCALE	SHEET	REV
1:1	1 OF 1	0