









REV.	DESCRIPTION	ECN NO.	NAME	DATE



NOTES:

1. 20 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE ± 0.2 .
2. MATERIAL: CLARITY CONDUCTIVE POLYSTYRENE ALLOY
100% RECYCLABLE.
3. ALL DIMENSIONS MEET EIA-481-3 REQUIREMENTS.
4. THICKNESS: 0.25 ± 0.05 MM
5. COMPONENT LOAD PER 30.2M" REEL: 1000PCS.
6. 10REEL/CARTON: 10000PCS

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. TOL. .X ±0.25 .XX ±0.15 .XXX ±0.10 GENERAL ANGLE: ±3°		TITLE: T-FLASH CARD 1.6H(掀盖式)					
		DWG. NO.: TF-102-GZ8PH16		CHECKED: MAX			
		PART NO.: TF-102-GZ8PH16		DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 2 of 2	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL

