



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Tab**
Mating Tab Width: **1.02 mm [.02 in]**
Mating Tab Thickness: **.51 mm [.02 in]**
Magnet Wire Size: **.13 – .36 mm**

Features

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Dimensions

Terminal Height	3.18 mm[.125 in]
Magnet Wire Size	.13 – .36 mm
Stock Thickness (Magnet Wire Side)	.51 mm[.02 in]
Product Length	8.76 mm[.345 in]

Product Type Features

Compatible With Discrete Wire Type	Solid, Magnet Wire
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	Tab
Mating Tab Width	1.02 mm[.02 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Plating Material	Tin
Contact Underplating Material	Nickel



Terminal Orientation	Straight
----------------------	----------

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Retention Type	Barbs
-----------------------	-------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1601119-2
118X 025 TAB FINE WIRE SIAMEZE

TE Part # 1601009-5
TAB,PCB,STD,SMZ

TE Part # 2-1601119-2
118X025 TAB FINE WIRE SIAMEZE

TE Part # 1601424
531-006-000=POCKET SPECIFICATION

Also in the Series | SIAMEZE

Insertion & Extraction Tools(1)

Magnet Wire Terminals(191)

Customers Also Bought

TE Part #3-643816-8
08P MTA100 CONN ASSY POL RIB

TE Part #1-966067-2
FER,WIRE,PL SLV,1.50/16,L8,BLACK,LP

TE Part #1601037-2
131-083-010=TAB,059X032,STD SMZ

TE Part #3-641191-8
08P MTA100 CONN ASSY WHT LF

TE Part #936394-2
2.8MM SLD 6P PLUG ASSY

TE Part #2141826-1
MQS0,63 Sn rec LL EDS 0,08-0,22

TE Part #3-647002-8
08P MTA100 PSTD CONN ASSY LF

TE Part #1601214-2
TAB,PCB,STD,SIAMEZE



Documents

Product Drawings

TAB,PCB,FINE,SMZ

English

TAB,PCB,FINE,SMZ

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1601120-4_E_c-1601120-4-e.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1601120-4_E_c-1601120-4-e.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1601120-4_E_c-1601120-4-e.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

1-1773702-7 _IDC_Magnet_Wire

English

Product Specifications

Application Specification

English