SERIES: VGS-50C | **DESCRIPTION:** INTERNAL AC-DC POWER SUPPLY

FEATURES

- universal input range (85 ~ 264 VAC)
- UL/EN/IEC 62368 certified
- designed to meet IEC/EN 61558, IEC/EN 60335, and GB 4943 system requirements
- short-circuit, over-current, over-voltage protections
- CISPR/EN55032 Class B radiated/conducted emissions
- output adjustable via trimpot +/- 10%




MODEL

MODEL	output voltage (Vdc)	output current max (A)	output power max (W)	ripple and noise[1] typ (mVp-p)	efficiency[2] typ (%)
VGS-50C-5	5	10.0	50.0	80	86
VGS-50C-12	12	4.2	50.4	120	87
VGS-50C-15	15	3.4	51.0	120	88
VGS-50C-24	24	2.2	52.8	150	89
VGS-50C-36	36	1.45	52.2	200	89
VGS-50C-48	48	1.1	52.8	200	90

Notes: 1. Ripple & noise are measured at 20 MHz BW with 47 µF aluminum electrolytic capacitor and 0.1 µF ceramic capacitor on the output.
2. Measured at 230 Vac

PART NUMBER KEY



Please read our datasheet & drawing disclaimer here.

INPUT

parameter	conditions/description	min	typ	max	units
voltage	ac input dc input	85 120		264 373	Vac Vdc
frequency		47		63	Hz
current	at 115 Vac at 230 Vac			1.2 0.8	A A
inrush current	at 115 Vac, cold start at 230 Vac, cold start		30 50		A A
leakage current	at 240 Vac			0.75	mA
no load power consumption				0.3	W

OUTPUT

parameter	conditions/description	min	typ	max	units
capacitive load	5 Vdc output 12 Vdc output 15 Vdc output 24 Vdc output 36 Vdc output 48 Vdc output			8,500 2,000 1,500 1,000 800 680	µF µF µF µF µF µF
initial set point accuracy	5 Vdc output, full load other outputs, full load		±2 ±1		% %
line regulation			±0.5		%
load regulation	0%~100% load 5 Vdc output other outputs		 ±1 ±0.5		 % %
adjustability	built in trim pot	±10			%
hold-up time	at 115 Vac at 230 Vac	8 30			ms ms
switching frequency			65		kHz
temperature coefficient			±0.03		%/°C

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over voltage protection	5 Vdc output, clamp 12 Vdc output, clamp 15 Vdc output, clamp 24 Vdc output, clamp 36 Vdc output, clamp 48 Vdc output, clamp			6.3 16.2 21.75 33.6 48.6 60.0	Vdc Vdc Vdc Vdc Vdc Vdc
over current protection	auto-recovery	110		200	%
short circuit protection	hiccup, continuous, auto-recovery				

SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to ground input to output output to ground	2,000 4,000 1,250			Vac Vac Vac
safety approvals	certified to: 62368: IEC/EN/UL designed to meet: 60335: IEC/EN designed to meet: 61558: IEC/EN designed to meet: 4943: GB				
safety class	Class I				
EMI/EMC	CISPR32/EN55032 Class B, IEC/EN61000-3-2 Class A				
ESD	IEC/EN 61000-4-2 Contact ±6KV /Air ±8KV, perf. Criteria A				

SAFETY & COMPLIANCE

radiated immunity	IEC/EN 61000-4-3 10V/m, perf. Criteria A		
EFT/burst	IEC/EN 61000-4-4 ±2KV, perf. Criteria A		
surge	IEC/EN 61000-4-5 line to line ±2KV/line to ground ±4KV, perf. Criteria A		
conducted immunity	IEC/EN61000-4-6 10 Vr.m.s, perf. Criteria A		
voltage dips and interruptions	IEC/EN61000-4-11 0%, 70%, perf. Criteria B		
MTBF	as per MIL-HDBK-217F at 25°C	300,000	hours
RoHS	yes		

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature		-30		70	°C
storage temperature		-40		85	°C
operating humidity	non-condensing	20		90	%
storage humidity	non-condensing	0		95	%


MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	99.00 x 82.00 x 30.00				mm
weight			180		g
cooling	natural convection				
case material	metal (AL1100, SGCC)				

MECHANICAL DRAWING

units: mm [inch]
tolerance: ±1.0 [±0.039]
wire range: 22-12 AWG
connector tightening torque: M3.5, 0.8 N·m

PIN CONNECTIONS	
PIN	Function
1	AC(L)
2	AC(N)
3	⏚
4	-Vo
5	+Vo




Position	Screw spec.	L (max)	Torque (max)
② - ③	M3	5 mm	0.4 N·m
⑥ - ⑦	M3	3 mm	0.4 N·m


Note: At least one hole position, ①~⑧, must be securely connected to Protective Earth (PE) ⏚

DERATING CURVE

TEMPERATURE DERATING CURVE




INPUT VOLTAGE DERATING CURVE (25°C)




EFFICIENCY CURVES

EFFICIENCY VS INPUT VOLTAGE (full load)



EFFICIENCY VS OUTPUT LOAD (Vin = 230 Vac)



REVISION HISTORY

rev.	description	date
1.0	initial release	09/28/2020
1.01	derating and efficiency curves updated	02/10/2022
1.02	UKCA mark added	06/06/2022

The revision history provided is for informational purposes only and is believed to be accurate.

CUI INC
a bel group

Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.