

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


LOC	DIST
-	-

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST RELEASED	03SEP2019	WH	DZ










1. MATERIAL: NYLON UL94V-0, FLAME RETARDANT
2. PART COLOR VARIES IN TINT AND MAY APPEAR UNEVENLY MIXED
3. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION.ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR
4. ACCEPTS TE PIN CONTACTS: 2238007-[ ] OR 2238008-[ ]
5. HOUSING ACCEPTS OPTIONAL TPA:[ ]-1969443-[ ] OR [ ]-1969825-[ ]
6. RECOMMENDED MATING PART:[ ]-2338183-[ ]
7. PACKAGING: LOOSE PIECE.









POS	DIM.C	DIM.B	DIM.A	PART NUMBER (RED COLOR)	PART NUMBER (BLUE COLOR)	PART NUMBER (BLACK COLOR)	PART NUMBER (YELLOW COLOR)	PART NUMBER (GREEN COLOR)
15	41.00	40.00	38.00	1-2349952-5	3-2349952-5	5-2349952-5	7-2349952-5	9-2349952-5
14	38.50	37.50	35.50	1-2349952-4	3-2349952-4	5-2349952-4	7-2349952-4	9-2349952-4
13	36.00	35.00	33.00	1-2349952-3	3-2349952-3	5-2349952-3	7-2349952-3	9-2349952-3
12	33.50	32.50	30.50	1-2349952-2	3-2349952-2	5-2349952-2	7-2349952-2	9-2349952-2
11	31.00	30.00	28.00	1-2349952-1	3-2349952-1	5-2349952-1	7-2349952-1	9-2349952-1
10	28.50	27.50	25.50	1-2349952-0	3-2349952-0	5-2349952-0	7-2349952-0	9-2349952-0
9	26.00	25.00	23.00	2349952-9	2-2349952-9	4-2349952-9	6-2349952-9	8-2349952-9
8	23.50	22.50	20.50	2349952-8	2-2349952-8	4-2349952-8	6-2349952-8	8-2349952-8
7	21.00	20.00	18.00	2349952-7	2-2349952-7	4-2349952-7	6-2349952-7	8-2349952-7
6	18.50	17.50	15.50	2349952-6	2-2349952-6	4-2349952-6	6-2349952-6	8-2349952-6
5	16.00	15.00	13.00	2349952-5	2-2349952-5	4-2349952-5	6-2349952-5	8-2349952-5
4	13.50	12.50	10.50	2349952-4	2-2349952-4	4-2349952-4	6-2349952-4	8-2349952-4
3	11.00	10.00	8.00	2349952-3	2-2349952-3	4-2349952-3	6-2349952-3	8-2349952-3
2	8.50	7.50	5.50	2349952-2	2-2349952-2	4-2349952-2	6-2349952-2	8-2349952-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±0.20
3 PLC ±-
4 PLC ±-
ANGLES ±5°

MATERIAL 1 -

FINISH -

DWN WARREN HUO 18FEB2019
CHK DANIEL ZHANG 18FEB2019
APVD DANIEL ZHANG 18FEB2019
PRODUCT SPEC 108-2418
APPLICATION SPEC 114-13315
WEIGHT -

TE Connectivity

NAME CAP HOUSING, WTW, PANEL MOUNT ALL COLOR, UL VERSION, SINGLE ROW ECONOMY POWER 2.5

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2349952	-

CUSTOMER DRAWING | SCALE N/A | SHEET 1 OF 2 | REV A


printed on 27 Dec 2023 09:40 (China Standard Time) from TE311234

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


LOC	DIST
-	-

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




2 POSITION
2349952-2




3 POSITION
2349952-3



4 POSITION
2349952-4



5 POSITION
2349952-5



6 - 15 POSITION
2349952-6 TO 1-2349952-5

printed on 27 Dec 2023 09:40 (China Standard Time) from TE311234

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±0.20
3 PLC ±-
4 PLC ±-
ANGLES ±5°

MATERIAL -

FINISH -

DWN	18FEB2019 WARREN HUO
CHK	18FEB2019 DANIEL ZHANG
APVD	18FEB2019 DANIEL ZHANG
PRODUCT SPEC	108-2418
APPLICATION SPEC	114-13315
WEIGHT	-

TE Connectivity

NAME: CAP HOUSING, WTW, PANEL MOUNT ALL COLOR, UL VERSION, SINGLE ROW ECONOMY POWER 2.5

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2349952	-

CUSTOMER DRAWING | SCALE N/A | SHEET 2 OF 2 | REV A