


REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
C	REVISED PER ECO-14-008930	06/12/2014	I. MYONG




3 POSITION




4 POSITION




5 POSITION



6 POSITION



7 POSITION



8 POSITION

©2014 TE CONNECTIVITY LTD. FAMILY OF COMPANIES. ALL RIGHTS RESERVED
TE CONNECTIVITY (LOGO) AND TE (LOGO) ARE TRADEMARKS.
OTHER LOGOS, PRODUCT AND/OR COMPANY NAMES MAY BE TRADEMARKS OF THEIR RESPECTIVE OWNERS.

Raychem Adapters
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE IN BRACKETS AS REFERENCE.

TYCO ELECTRONICS RESERVES THE RIGHT TO CHANGE THIS DRAWING AT ANYTIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.

DECIMAL TOLERANCES:
.XXX ±.010 [0,25mm]
.XX ±.02 [0,51mm]
.X ±.1 [2,54mm]
ANGULAR TOLERANCE:
.X ±1°

DRAWN	P. TALLY	DATE 02/16/2007
CHECKED	M. PIOZET	DATE 02/16/2007
APPROVED	I. MYONG	DATE 08/14/2009

CAD FILE NAME: FLX40-02X-XX.dwg


THIRD ANGLE PROJECTION:

TE CONNECTIVITY


TITLE
STAR, MULTI-POSITION HEXASHIELD-F
EMI TERMINATION SYSTEM

SIZE	CAGE	DWG. NO.	REV
A	06090	FLX40-02X-XX	C


DO NOT SCALE THIS DRAWING | SHEET 1 OF 6




9 POSITION



10 POSITION






SECTION A–A

14 POSITION


Raychem Adapters
CUSTOMER DRAWING

TE	DO NOT SCALE THIS DRAWING	SIZE A	CAGE 06090	SHEET 2 OF 6	DWG. NO. FLX40–02X–XX	REV C



SECTION A–A

15 POSITION




SECTION A–A

18 POSITION


Raychem Adapters
CUSTOMER DRAWING

	DO NOT SCALE THIS DRAWING	SIZE	CAGE	SHEET	DWG. NO.	REV
TE		A	06090	3 OF 6	FLX40–02X–XX	C



SECTION A–A

19 POSITION




SECTION A–A

20 POSITION


Raychem Adapters
CUSTOMER DRAWING

TE	DO NOT SCALE THIS DRAWING	SIZE A	CAGE 06090	SHEET 4 OF 6	DWG. NO. FLX40–02X–XX	REV C



SECTION A–A

25 POSITION



SECTION A–A

30 POSITION

Raychem Adapters
CUSTOMER DRAWING

TE	DO NOT SCALE THIS DRAWING	SIZE A	CAGE 06090	SHEET 5 OF 6	DWG. NO. FLX40–02X–XX	REV C

MATERIAL:

BASE METAL – ALUMINUM ALLOY 6061–T651 OR EN AW 2011–T3.

PLATINGS:

– ELECTROLESS NICKEL CONFORMING TO SAE AMS–C–26074, CLASS 4, GRADE C.

– CADMIUM OLIVE OLIVE DRAB CONFORMING TO SAE AMS–QQ–P–416 TYPE III, CLASS 3 (500 HOUR SALT SPRAY).

APPLICATION:

1. THESE DEVICES ARE DESIGNED TO BE USED IN A HEXASHIELD–F EMI TERMINATION SYSTEM.

PART NUMBERING:

FLX40-02X-XX

- 03: STAR, 3 POSITION
- 04: STAR, 4 POSITION
- 05: STAR, 5 POSITION
- 06: STAR, 6 POSITION
- 07: STAR, 7 POSITION
- 08: STAR, 8 POSITION
- 09: STAR, 9 POSITION
- 10: STAR, 10 POSITION
- 14: STAR, 14 POSITION
- 15: STAR, 15 POSITION
- 18: STAR, 18 POSITION
- 19: STAR, 19 POSITION
- 20: STAR, 20 POSITION
- 25: STAR, 25 POSITION
- 30: STAR, 30 POSITION

- 0: ELECTROLESS NICKEL
- 1: CADMIUM OLIVE DRAB

Raychem Adapters
CUSTOMER DRAWING

	DO NOT SCALE THIS DRAWING	SIZE	CAGE	SHEET	DWG. NO.	REV
TE		A	06090	6 OF 6	FLX40–02X–XX	C