


### Features

- High Continuous Forward Current
- Low Reverse Current
- Very Low Forward Voltage Drop
- Very High Switching Speed



### Applications

- surface mount schottky barrier rectifier
- Buck and Boost dc-dc Converters
- Reverse Voltage and Current Protection
- Clamping & Protection



### Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Reverse Voltage	$V_R$	30	V
Forward Current (DC)	$I_F$	200	mA
Forward Surge Current (60 Hz @ 1 cycle)	$I_{FSM}$	4.0	A
ESD Rating: Human Body Model	ESD	>8.0	KV
ESD Rating: Machine Model		>400	V

### Thermal Characteristics

Parameter	Symbol	Value	Unit
Total Power Dissipation	PD	312	mW
Typical Thermal Resistance per leg @TA = 25°C	$R_{\theta JA}$	400	°C/W
Operating Junction Temperature Range	$T_J$	-40 to +125	°C
Storage Temperature Range	$T_{STG}$	-40 to +125	°C


Mounted onto a 4 in square FR-4 board 10 mm sq. 1 oz. Cu 0.06" thick single sided. Operating to steady state.

### Electrical Characteristics (TA=25°C unless otherwise specified)


Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Forward Voltage	$V_F^*$	--	--	0.37	V	$I_F=10\text{mA}$
		--	--	0.55	V	$I_F=200\text{mA}$
Reverse Leakage	$I_R^{**}$	--	--	7	uA	$V_R = 10\text{V}$
		--	--	50	uA	$V_R = 30\text{V}$
Total Capacitance	$C_T$	--	7.0	--	pF	$V_R = 5.0\text{V}, f = 1\text{MHz}$

\*Pulse width  $\leq 380\text{ uS}$ , Duty cycle  $< 2\%$ ; \*\*pulse test ,  $t_p \leq 5\text{ms}$

Typical Electrical Characteristic Curves




**Outline Drawing - CSP0201**



SYM	DIMENSIONS		
	MILLIMETERS		
	MIN	NOM	MAX
A	0.230	0.300	0.330
A1	0.000	0.020	0.050
b	0.215	0.245	0.275
c	0.120	0.150	0.180
D	0.550	0.600	0.650
e	0.355 BSC		
E	0.250	0.300	0.350
L	0.160	0.190	0.220
h	0.079 BSC		

**Suggested Land Pattern**



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
X	0.30	0.012
Y1	0.25	0.010
Y2	0.15	0.006
Y3	0.40	0.016
Z	0.65	0.026